

Handflex Cable, MCX RA to MCX RA, 12"

086-12MCR+

Typical Performance Data

FREQ.	INSERTION LOSS	Right Angle MCX VSWR	Right Angle MCX VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	-0.07	1.01	1.01
0.10	-0.13	1.03	1.03
0.20	-0.17	1.02	1.01
0.40	-0.22	1.05	1.04
0.60	-0.26	1.03	1.03
0.80	-0.29	1.04	1.02
1.00	-0.32	1.07	1.07
1.20	-0.34	1.03	1.04
1.40	-0.36	1.08	1.07
1.60	-0.38	1.08	1.09
1.80	-0.39	1.05	1.04
2.00	-0.42	1.11	1.12
2.20	-0.43	1.06	1.07
2.40	-0.45	1.10	1.09
2.60	-0.47	1.10	1.11
2.80	-0.47	1.07	1.07
3.00	-0.49	1.11	1.12
3.20	-0.50	1.07	1.08
3.40	-0.51	1.11	1.11
3.60	-0.52	1.06	1.08
3.80	-0.54	1.11	1.10
4.00	-0.55	1.08	1.09
4.20	-0.56	1.09	1.09
4.40	-0.58	1.12	1.12
4.60	-0.58	1.06	1.08
4.80	-0.60	1.15	1.15
5.00	-0.61	1.08	1.09
5.20	-0.62	1.13	1.13
5.40	-0.64	1.16	1.17
5.60	-0.63	1.08	1.09
5.80	-0.67	1.20	1.21
6.00	-0.66	1.11	1.14



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
086-12MCR+
8/25/2026
Page 1 of 1