

Handflex Cable, MCX RA to MCX RA, 18"

086-18MCR+

Typical Performance Data

FREQ.	INSERTION LOSS	Right Angle MCX VSWR	Right Angle MCX VSWR
(GHz)	(dB)	(:1)	(:1)
0.01	-0.08	1.01	1.01
0.10	-0.16	1.03	1.03
0.20	-0.21	1.01	1.02
0.40	-0.28	1.01	1.02
0.60	-0.34	1.01	1.02
0.80	-0.38	1.02	1.02
1.00	-0.42	1.04	1.02
1.20	-0.45	1.05	1.03
1.40	-0.48	1.06	1.05
1.60	-0.52	1.08	1.08
1.80	-0.55	1.09	1.10
2.00	-0.58	1.10	1.11
2.20	-0.60	1.10	1.11
2.40	-0.62	1.08	1.10
2.60	-0.64	1.07	1.07
2.80	-0.66	1.06	1.06
3.00	-0.67	1.06	1.06
3.20	-0.70	1.07	1.08
3.40	-0.72	1.09	1.10
3.60	-0.74	1.09	1.11
3.80	-0.76	1.09	1.10
4.00	-0.77	1.07	1.09
4.20	-0.79	1.07	1.08
4.40	-0.81	1.07	1.08
4.60	-0.83	1.09	1.10
4.80	-0.85	1.12	1.14
5.00	-0.87	1.13	1.14
5.20	-0.88	1.12	1.13
5.40	-0.89	1.08	1.11
5.60	-0.90	1.07	1.09
5.80	-0.92	1.07	1.09
6.00	-0.94	1.11	1.13



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
086-18MCR+
8/25/2026
Page 1 of 1