

Handflex Cable, SMA RA to MCX RA, 18"

086-18SMRMCR+

Typical Performance Data

FREQ.	INSERTION LOSS	Right Angle SMA VSWR	Right Angle MCX VSWR
(GHz)	(dB)	(:1)	(:1)
0.10	-0.12	1.02	1.02
0.20	-0.17	1.01	1.01
0.40	-0.25	1.01	1.01
0.60	-0.31	1.02	1.02
0.80	-0.37	1.02	1.03
1.00	-0.42	1.02	1.03
1.20	-0.46	1.02	1.04
1.40	-0.50	1.03	1.05
1.60	-0.54	1.03	1.06
1.80	-0.57	1.03	1.06
2.00	-0.60	1.03	1.05
2.20	-0.64	1.04	1.07
2.40	-0.66	1.04	1.07
2.60	-0.69	1.05	1.08
2.80	-0.72	1.06	1.09
3.00	-0.75	1.07	1.09
3.20	-0.78	1.09	1.11
3.40	-0.80	1.09	1.12
3.60	-0.82	1.09	1.12
3.80	-0.84	1.09	1.13
4.00	-0.86	1.10	1.13
4.20	-0.88	1.10	1.14
4.40	-0.90	1.11	1.15
4.60	-0.93	1.12	1.16
4.80	-0.95	1.13	1.16
5.00	-0.98	1.13	1.16
5.20	-1.00	1.13	1.16
5.40	-1.02	1.13	1.16
5.60	-1.03	1.13	1.16
5.80	-1.04	1.12	1.16
6.00	-1.06	1.13	1.16



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
086-18SMRMCR+
8/26/2026
Page 1 of 1