

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10.0	0.02	38.5	42.3
50.0	0.09	41.1	40.3
100.0	0.12	42.3	41.7
140.0	0.15	44.9	46.0
260.0	0.21	46.2	40.9
300.0	0.22	46.2	43.1
340.0	0.24	54.0	57.4
380.0	0.25	53.5	44.9
460.0	0.28	43.5	40.2
500.0	0.30	47.4	46.3
550.0	0.31	51.5	48.7
600.0	0.32	42.2	40.0
650.0	0.34	42.2	41.6
700.0	0.35	51.6	53.1
750.0	0.36	44.3	40.6
800.0	0.38	40.7	38.8
850.0	0.39	44.6	45.0
900.0	0.40	55.7	48.7
950.0	0.41	42.1	39.5
1000.0	0.43	42.4	41.3
1200.0	0.47	45.7	47.0
1400.0	0.51	51.4	51.7
1500.0	0.53	37.8	38.2
1600.0	0.55	41.7	41.5
1800.0	0.59	38.9	39.3
2000.0	0.62	36.7	37.9
2400.0	0.69	37.3	39.1
2600.0	0.71	46.5	50.8
3000.0	0.77	36.5	39.5
3400.0	0.83	33.6	35.5
3600.0	0.85	34.3	36.1
4000.0	0.90	39.8	43.3
4400.0	0.95	35.9	37.7
4600.0	0.97	34.2	38.0
5000.0	1.01	33.9	36.5
5400.0	1.06	34.7	34.9
5600.0	1.08	39.9	40.6
6000.0	1.12	35.5	39.1
6400.0	1.16	33.5	38.0
6600.0	1.19	41.1	46.3
7000.0	1.22	43.2	42.3
7400.0	1.25	39.3	45.5
7600.0	1.28	34.1	41.2
8000.0	1.30	36.8	43.9
8400.0	1.33	36.9	36.7
8600.0	1.35	33.3	34.2
9000.0	1.39	30.9	36.6
9200.0	1.41	29.2	41.8
9400.0	1.44	32.5	38.0
9600.0	1.45	29.8	31.0
10000.0	1.52	26.1	26.3
11600.0	1.66	27.4	30.1
12000.0	1.71	28.2	29.3
12400.0	1.76	22.0	24.7
12800.0	1.78	24.9	25.0
13600.0	1.88	23.0	24.4
14000.0	1.92	21.0	22.2
14400.0	1.92	25.7	27.4
15600.0	2.02	24.7	27.9
16000.0	2.00	25.7	28.8
16400.0	2.05	24.0	25.2
16800.0	2.06	25.3	31.7
17600.0	2.11	24.8	25.4
18000.0	2.10	28.2	30.7