

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.02	42.6	42.4
200.0	0.03	38.0	38.2
300.0	0.04	36.0	36.2
400.0	0.05	34.9	35.2
500.0	0.06	34.7	34.9
600.0	0.06	35.1	35.1
700.0	0.07	36.0	35.9
800.0	0.07	37.5	37.4
900.0	0.08	39.5	39.6
1000.0	0.09	42.3	42.2
1100.0	0.09	44.9	45.6
1250.0	0.10	44.8	48.5
1500.0	0.11	40.9	43.8
1750.0	0.11	42.1	43.1
2000.0	0.12	48.8	43.0
2001.0	0.12	48.9	43.1
2250.0	0.13	43.6	42.7
2500.0	0.14	39.4	42.0
2750.0	0.14	40.2	41.0
3000.0	0.15	47.2	38.7
3250.0	0.15	41.1	35.5
3500.0	0.16	34.7	33.3
3750.0	0.17	32.8	32.5
4000.0	0.17	33.6	33.2
4250.0	0.18	37.9	35.8
4500.0	0.18	39.0	35.5
5000.0	0.19	31.1	30.1
5500.0	0.19	32.3	33.5
6000.0	0.20	38.5	35.1
6500.0	0.20	29.5	29.5
7000.0	0.20	31.9	35.7
7500.0	0.20	34.8	32.9
8000.0	0.22	27.0	29.0
8500.0	0.22	32.6	30.6
9000.0	0.23	27.1	28.6
9500.0	0.22	28.5	30.4
10000.0	0.22	29.0	28.1
10500.0	0.23	26.2	31.4
11000.0	0.19	38.9	30.4
11500.0	0.23	24.6	28.1
12000.0	0.20	31.9	32.0
12500.0	0.25	26.9	35.9
13000.0	0.16	31.0	33.4
13500.0	0.24	27.3	32.3
14000.0	0.18	28.1	41.1
14500.0	0.19	30.5	33.9
15000.0	0.23	26.1	28.2
15500.0	0.24	23.9	27.4
16000.0	0.19	29.4	35.6
16500.0	0.24	21.5	22.4
17000.0	0.24	22.3	27.1
17500.0	0.25	28.0	26.3
18000.0	0.29	21.3	23.2