

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10.0	0.00	47.9	47.8
50.0	0.01	48.3	53.0
100.0	0.02	48.5	46.6
150.0	0.02	48.7	46.0
200.0	0.03	48.7	44.4
250.0	0.03	47.8	43.0
300.0	0.04	47.7	42.5
350.0	0.04	47.0	41.2
400.0	0.04	46.1	40.3
450.0	0.05	45.6	39.6
500.0	0.05	44.7	39.0
550.0	0.05	43.7	38.6
600.0	0.05	43.0	38.4
650.0	0.06	42.4	38.1
700.0	0.06	41.9	38.1
750.0	0.06	41.3	38.4
800.0	0.06	40.9	38.7
850.0	0.07	40.6	39.3
900.0	0.07	40.3	39.7
950.0	0.07	40.4	40.7
1000.0	0.07	40.5	41.8
1200.0	0.08	42.8	51.9
1400.0	0.09	44.1	42.9
1600.0	0.09	38.7	36.2
1800.0	0.10	34.7	33.3
2000.0	0.11	32.7	32.6
2200.0	0.11	32.5	33.2
2400.0	0.12	34.1	36.1
2600.0	0.12	39.2	45.4
2800.0	0.12	57.6	44.4
3000.0	0.13	37.6	35.0
3600.0	0.14	30.9	32.1
4000.0	0.15	38.4	42.2
4600.0	0.16	32.6	31.6
5000.0	0.17	32.6	33.6
5600.0	0.18	36.0	33.0
6000.0	0.19	31.2	29.2
6600.0	0.20	34.8	42.7
7000.0	0.20	37.6	33.4
7600.0	0.22	31.0	32.9
8000.0	0.23	35.4	49.4
8600.0	0.23	30.4	30.6
9000.0	0.25	29.0	29.5
9600.0	0.25	35.1	38.2
10000.0	0.27	25.9	25.8
10600.0	0.28	28.6	29.2
11000.0	0.28	32.9	35.0
11600.0	0.31	23.3	23.9
12000.0	0.31	27.0	27.4
12600.0	0.32	26.5	28.0
13000.0	0.35	22.0	22.5
13600.0	0.33	29.4	29.4
14000.0	0.34	28.6	28.2
14600.0	0.39	20.8	21.0
15000.0	0.37	25.1	24.9
15600.0	0.39	24.6	24.8
16000.0	0.43	20.4	20.0
16600.0	0.39	30.0	30.1
17000.0	0.44	22.3	22.0
17600.0	0.45	20.1	19.1
18000.0	0.42	25.7	25.1