

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.05	40.9	40.7
200.0	0.08	40.3	41.0
300.0	0.10	46.5	49.0
400.0	0.12	48.5	50.8
500.0	0.14	42.3	42.3
600.0	0.15	42.1	42.3
700.0	0.16	48.5	49.5
800.0	0.17	48.5	51.4
900.0	0.19	41.9	42.7
1000.0	0.20	41.9	43.1
1100.0	0.21	47.8	50.6
1250.0	0.22	42.9	44.8
1500.0	0.24	45.0	50.6
1750.0	0.27	37.6	39.2
2000.0	0.29	45.6	49.4
2250.0	0.31	36.4	37.9
2500.0	0.32	38.3	38.4
2750.0	0.34	35.1	36.7
3000.0	0.35	36.2	35.8
3250.0	0.37	40.1	42.6
3500.0	0.39	32.3	32.6
3750.0	0.40	42.3	43.0
4000.0	0.41	32.6	32.7
4250.0	0.42	44.9	42.3
4500.0	0.44	32.9	33.7
5000.0	0.46	32.8	33.2
5500.0	0.48	34.4	34.9
6000.0	0.50	42.9	40.5
6500.0	0.53	41.3	48.5
7000.0	0.55	41.8	44.4
7500.0	0.57	37.3	48.4
8000.0	0.59	36.5	42.9
8500.0	0.61	38.6	40.2
9000.0	0.63	35.6	35.5
9500.0	0.65	32.8	33.0
10000.0	0.66	28.9	30.2
10500.0	0.69	27.3	28.8
11000.0	0.70	28.3	29.0
11500.0	0.71	31.4	31.7
12000.0	0.72	42.6	45.1
12500.0	0.73	39.2	47.0
13000.0	0.75	30.2	32.9
13500.0	0.79	23.0	24.7
14000.0	0.80	24.2	25.8
14500.0	0.84	20.4	21.4
15000.0	0.84	21.9	23.1
15500.0	0.84	30.4	31.6
16000.0	0.87	24.6	25.4
16500.0	0.87	36.3	36.5
17000.0	0.88	32.9	33.2
17500.0	0.93	24.8	25.9
18000.0	0.93	24.6	25.7