

# Non-Magnetic Flex Cable SMA Male to SMA Male

# 141N-20CSM

## Typical Performance Data

FREQ.	INSERTION LOSS	SMA MALE RETURN LOSS IN	SMA MALE RETURN LOSS OUT
(GHz)	(dB)	(dB)	(dB)
0	0.01	57.65	56.24
1	0.07	45.07	45.17
2	0.10	43.81	43.45
3	0.13	44.51	45.62
4	0.16	46.73	47.13
5	0.18	35.12	35.30
6	0.20	32.87	32.80
7	0.22	37.27	37.84
8	0.24	39.05	38.89
9	0.26	38.22	37.73
10	0.28	34.73	34.24
11	0.29	34.17	34.24
12	0.31	30.75	30.48
13	0.33	27.74	27.63
14	0.34	32.76	33.58
15	0.36	33.19	33.91
16	0.38	30.34	30.14
17	0.39	24.59	24.33
18	0.41	22.95	22.93



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site  
 The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)



IF/RF MICROWAVE COMPONENTS