

Voltage Controlled Oscillator

ZX95-6030CR-S+

50Ω 5890 to 6010 MHz

The Big Deal:

- Low Phase Noise
- Linear Tuning
- Good Pulling & Pushing
- Robust design and construction
- Rigid unibody construction



Generic photo used for illustration purposes only

CASE STYLE: GB956

Product Overview:

The ZX95-6030CR-S+ is a Voltage Controlled Oscillator, designed to operate from 5890 to 6010 MHz for instrumentation applications. The ZX95-6030CR-S+ is built using Mini-Circuits proven unibody construction (size of 1.20" x .75" x .46") which integrates the RF connectors with the case body to shield against unwanted signals and noise.

Key Features

Feature	Advantages
Linear Tuning Sensitivity Ratio: 1.15:1 typ.	Optimal for loop filter design.
Low Phase Noise: -102 dBc/Hz typ at 10 kHz offset	Low phase noise improves system EVM (Error Vector Magnitude).
Good Pulling, 2 MHz typ.	Improves immunity against changes in output load.
Good Pushing, 1.4 MHz/V typ.	Provides increased immunity against noisy DC lines and improves output frequency stability vs. variations in supply voltage.

2x Fundamental

Voltage Controlled Oscillator

ZX95-6030CR-S+

Frequency Doubling 5890 to 6010 MHz

Features

- frequency based on multiplication of carrier frequency
- low phase noise, -102 dBc/Hz typ. @ 10kHz offset
- linear tuning characteristics
- low pulling, 2 MHz typ.
- low pushing, 1.4 MHz/V typ.
- protected by US patent 6,790,049

Applications

- r & d
- lab
- instrumentation
- point-to-point radio



Generic photo used for illustration purposes only

CASE STYLE: GB956

Connectors Model

SMA ZX95-6030CR-S+

+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications


Electrical Specifications

MODEL NO.	FREQ. (MHz)		POWER OUTPUT (dBm)	PHASE NOISE dBc/Hz SSB at offset frequencies,kHz				TUNING					NON HARMONIC SPURIOUS (dBc)	HARMONICS (dBc)			PULLING pk-pk @12 dB _r (MHz)	PUSHING (MHz/V)	DC OPERATING POWER		
	F2x (1/2F)			Typ.				VOLTAGE RANGE (V)		SENSI- TIVITY (MHz/V) (pF)		3 dB MODULATION BANDWIDTH (MHz)		Max.					V _{cc} (volts)	Current (mA)	
	Min.	Max.		Typ.	1	10	100	1000	Min.	Max.	Typ.	Typ.		Typ.	Typ.	F0.5			F1.5	F2	Typ.
ZX95-6030CR-S+	5890	6010	+3.5	-73	-102	-124	-144	0.5	5	63	73	12	140	-90	-27	-25	-22	2	1.4	5	28

Maximum Ratings

Operating Temperature	-55°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Supply Voltage (Vcc)	7V
Absolute Max. Tuning Voltage (Vtune)	7V
All specifications	50 ohm system







Permanent damage may occur if any of these limits are exceeded.

NOTE: When soldering the DC connections, caution must be used to avoid overheating the DC terminals. See Application Note [AN-40-10](#).**Outline Drawing****Outline Dimensions (inch mm)**

A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	S	T	wt.
1.20	.75	.46	1.18	.04	.38	.38	.57	.18	.33	.21	.22	.08	1.00	.50	.35	.18	.106	grams
30.48	19.15	11.61	30.07	1.02	9.53	9.53	14.43	4.62	8.31	5.28	5.59	2.03	25.40	12.70	8.89	4.57	2.69	35.0

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			Icc (mA)	HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ. PULL (MHz)	PHASE NOISE (dBc/Hz) at offsets				FREQ OFFSET (kHz)	PHASE NOISE at 5950 MHz (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C		F0.5	F1.5	F2			1kHz	10kHz	100kHz	1MHz		
0.00	63.16	5808.7	5796.1	5782.6	3.94	2.74	1.31	17.95	-41.3	-45.3	-30.4	0.20	1.29	-72.28	-102.2	-125.2	-146.6	1.0	-74.17
0.50	56.46	5837.9	5826.4	5814.3	4.22	3.01	1.63	18.10	-40.9	-44.5	-30.6	0.35	1.88	-75.96	-104.4	-126.7	-147.3	2.5	-84.23
0.75	57.11	5852.2	5840.5	5828.6	4.48	3.14	1.78	18.15	-40.9	-47.3	-29.4	0.38	2.06	-75.11	-104.4	-126.5	-146.3	3.6	-89.58
1.00	57.95	5866.7	5854.8	5842.6	4.63	3.38	1.91	18.18	-41.0	-50.1	-30.2	0.41	1.68	-73.45	-103.5	-126.9	-146.3	6.0	-95.84
1.25	58.60	5881.1	5869.3	5856.8	4.67	3.54	2.09	18.22	-41.2	-48.4	-30.2	0.44	0.73	-74.52	-103.2	-126.7	-145.8	8.4	-99.49
1.50	58.58	5895.6	5883.9	5871.3	4.63	3.60	2.26	18.26	-41.2	-47.0	-30.2	0.44	1.34	-73.24	-102.8	-125.7	-146.7	10.0	-102.45
1.75	58.93	5910.0	5898.6	5886.1	4.68	3.59	2.36	18.32	-41.2	-49.6	-29.3	0.43	1.99	-74.01	-103.1	-127.6	-148.2	23.1	-111.98
2.00	60.13	5924.7	5913.3	5900.9	4.82	3.64	2.34	18.37	-41.2	-51.8	-29.1	0.41	1.89	-73.84	-103.0	-127.9	-147.0	38.8	-117.33
2.25	63.20	5940.2	5928.3	5915.9	4.93	3.77	2.39	18.41	-41.1	-51.5	-29.2	0.40	1.55	-74.17	-102.9	-125.9	-146.7	64.0	-122.73
2.50	66.55	5956.4	5944.1	5931.3	4.97	3.89	2.51	18.43	-41.0	-48.9	-29.2	0.41	1.09	-72.10	-102.5	-127.1	-146.2	89.8	-125.15
2.75	68.53	5973.2	5960.8	5947.4	5.07	3.86	2.62	18.45	-40.9	-49.7	-29.1	0.40	1.54	-72.85	-102.1	-126.1	-146.7	100.0	-127.47
3.00	70.08	5990.4	5977.9	5964.4	5.14	4.03	2.62	18.49	-40.8	-53.7	-30.1	0.33	1.91	-72.54	-101.9	-125.9	-146.7	150.8	-128.23
3.25	72.66	6008.2	5995.4	5981.9	5.22	4.11	2.74	18.51	-41.0	-48.8	-27.8	0.21	1.97	-74.02	-102.0	-125.7	-147.1	177.0	-131.77
3.50	73.45	6026.4	6013.6	5999.8	5.16	4.18	2.83	18.53	-40.9	-50.1	-29.1	0.03	0.95	-73.86	-101.6	-125.8	-145.8	211.6	-131.26
3.75	74.11	6044.9	6032.0	6018.2	5.18	4.12	2.89	18.56	-40.8	-52.9	-29.1	0.43	1.27	-72.53	-101.3	-125.8	-147.3	297.1	-131.63
4.00	73.28	6063.2	6050.5	6036.7	5.30	4.09	2.83	18.57	-40.7	-48.6	-27.8	0.98	1.91	-71.99	-100.3	-124.9	-145.9	348.8	-134.47
4.25	73.57	6081.9	6068.8	6055.2	5.43	4.20	2.72	18.57	-40.7	-52.3	-26.5	1.66	1.85	-72.77	-100.4	-124.9	-144.7	489.7	-140.60
4.50	70.36	6100.0	6087.2	6073.4	5.46	4.32	2.88	18.57	-40.5	-50.8	-27.6	2.38	0.69	-71.30	-100.3	-123.5	-144.0	585.4	-141.36
4.75	65.49	6117.1	6104.8	6091.3	5.29	4.36	2.99	18.58	-40.4	-51.9	-26.4	2.98	1.57	-70.98	-99.2	-122.8	-143.8	964.9	-146.49
5.00	61.03	6133.2	6121.2	6108.2	5.11	4.21	3.08	18.58	-40.1	-51.4	-26.3	3.38	1.97	-70.49	-98.9	-122.5	-143.4	1000.0	-146.24

*at 25°C unless mentioned otherwise



Additional Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Voltage Controlled Oscillator

ZX95-6030CR-S+

Typical Performance Data

V TUNE	TUNE SENS (MHz/V)	FREQUENCY (MHz)			POWER OUTPUT (dBm)			HARMONICS (dBc)			FREQ. PUSH (MHz/V)	FREQ OFFSET (kHz)	PHASE NOISE (dBc/Hz)
		-55°C	+25°C	+85°C	-55°C	+25°C	+85°C	F0.5	F1.5	F2			
0.00	63.2	5808.7	5796.1	5782.6	3.9	2.7	1.3	-41.3	-45.3	-30.4	0.2	1	-73
0.25	58.2	5823.6	5811.9	5799.2	4.1	2.9	1.5	-41.2	-45.1	-30.6	0.3	10	-102
0.50	56.5	5837.9	5826.4	5814.3	4.2	3.0	1.6	-40.9	-44.5	-30.6	0.4	100	-124
0.75	57.1	5852.2	5840.5	5828.6	4.5	3.1	1.8	-40.9	-47.3	-29.4	0.4	1000	-144
1.00	57.9	5866.7	5854.8	5842.6	4.6	3.4	1.9	-41.0	-50.1	-30.2	0.4		
1.25	58.6	5881.1	5869.3	5856.8	4.7	3.5	2.1	-41.2	-48.4	-30.2	0.4		
1.50	58.6	5895.6	5883.9	5871.3	4.6	3.6	2.3	-41.2	-47.0	-30.2	0.4		
1.75	58.9	5910.0	5898.6	5886.1	4.7	3.6	2.4	-41.2	-49.6	-29.3	0.4		
2.00	60.1	5924.7	5913.3	5900.9	4.8	3.6	2.3	-41.2	-51.8	-29.1	0.4		
2.25	63.2	5940.2	5928.3	5915.9	4.9	3.8	2.4	-41.1	-51.5	-29.2	0.4		
2.50	66.6	5956.4	5944.1	5931.3	5.0	3.9	2.5	-41.0	-48.9	-29.2	0.4		
2.75	68.5	5973.2	5960.8	5947.4	5.1	3.9	2.6	-40.9	-49.7	-29.1	0.4		
3.00	70.1	5990.4	5977.9	5964.4	5.1	4.0	2.6	-40.8	-53.7	-30.1	0.3		
3.25	72.7	6008.2	5995.4	5981.9	5.2	4.1	2.7	-41.0	-48.8	-27.8	0.2		
3.50	73.5	6026.4	6013.6	5999.8	5.2	4.2	2.8	-40.9	-50.1	-29.1	0.0		
3.75	74.1	6044.9	6032.0	6018.2	5.2	4.1	2.9	-40.8	-52.9	-29.1	0.4		
4.00	73.3	6063.2	6050.5	6036.7	5.3	4.1	2.8	-40.7	-48.6	-27.8	1.0		
4.25	73.6	6081.9	6068.8	6055.2	5.4	4.2	2.7	-40.7	-52.3	-26.5	1.7		
4.50	70.4	6100.0	6087.2	6073.4	5.5	4.3	2.9	-40.5	-50.8	-27.6	2.4		
4.75	65.5	6117.1	6104.8	6091.3	5.3	4.4	3.0	-40.4	-51.9	-26.4	3.0		
5.00	61.0	6133.2	6121.2	6108.2	5.1	4.2	3.1	-40.1	-51.4	-26.3	3.4		
5.25	61.2	6149.7	6136.4	6123.8	4.9	4.0	2.9	-39.8	-51.3	-26.7	3.7		
5.50	57.2	6165.0	6151.7	6138.1	5.0	3.7	2.7	-39.6	-54.9	-26.0	3.8		
5.75	50.3	6178.5	6166.0	6152.0	5.3	3.8	2.4	-39.6	-48.3	-26.1	3.7		
6.00	43.7	6190.4	6178.6	6165.4	5.5	4.0	2.4	-39.8	-47.9	-24.9	3.3		
6.25	38.3	6200.9	6189.6	6177.0	5.4	4.2	2.5	-40.1	-49.4	-26.0	2.9		
6.50	34.0	6210.4	6199.1	6187.1	5.2	4.2	2.7	-40.1	-53.1	-25.0	2.4		
6.75	30.5	6219.0	6207.6	6195.9	4.9	4.2	2.9	-40.1	-51.0	-24.9	1.9		
7.00	30.5	6226.8	6215.2	6203.6	4.7	4.0	2.9	-39.8	-48.1	-24.5	1.4		

Notes






- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
 B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
 C. The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCULStore/terms.jsp



Voltage Controlled Oscillator

ZX95-6030CR-S+

Typical Performance Data



Notes

- Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
- Electrical specifications and performance data contained in this specification document are based on Mini-Circuits' applicable established test performance criteria and measurement instructions.
- The parts covered by this specification document are subject to Mini-Circuits' standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCULStore/terms.jsp




Case Style

GB

Outline Dimensions

GB956



CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N
GB956	1.20 (30.48)	.75 (19.15)	.46 (11.61)	1.18 (30.07)	.04 (1.02)	.38 (9.53)	.38 (9.53)	.57 (14.43)	.18 (4.62)	.33 (8.31)	.21 (5.28)	.22 (5.59)	.08 (2.03)

CASE #.	P	Q	R	S	T	WT GRAMS
GB956	1.00 (25.4)	.50 (12.7)	.35 (8.89)	.18 (4.57)	.106 (2.69)	35

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3Pl. $\pm .015$
Tolerance on hole size and interaxes dimensions to be $\pm .005$.

Note:

1. Case material: Brass
2. Case finish: Nickel plate



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 85°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 100° C Ambient Environment	Individual Model Data Sheet
Barometric Pressure	100,000 Feet	MIL-STD-202, Method 105, Condition D
Humidity	90% RH, 65°C Units may require bake-out after humidity to restore full performance.	MIL-STD-202, Method 103
Thermal Shock	-65° to 125°C, 5 cycles	MIL-STD-202, Method 107, Condition B
Vibration (High Frequency)	20g peak, 10-2000 Hz, 12 times in each of three perpendicular directions (total 36)	MIL-STD-202, Method 204, Condition D
Mechanical Shock	100g, 6ms sawtooth, 3 shocks each direction 3 axes (total 18)	MIL-STD-202, Method 213, Condition I