

Coaxial Reflectionless High Pass Filter

ZXHF Series

50Ω

DC to 30 GHz



The Big Deal

- Patented design eliminates in band spurs
- Wideband performance up to 30 GHz

Product Overview

Mini-Circuits' ZXHF Series reflectionless filters employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. Reflectionless filters eliminate stopband reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators. This is developed in a new broadband, stable connectorized package.

Key Features

Feature	Advantages
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect pass band signals.
Excellent stability over temperature	Minimal variation in electrical performance across temperature.
Operating temperature up to 105°C	Suitable for operation close to high power components.
Broadband connectorized package	The connectorized package works well even in high frequencies and easy to interface with other devices. This is well suited for test setups.

Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp



High Pass Filter

50Ω 700 to 5000 MHz

ZXHF-K721M+



Generic photo used for illustration purposes only

CASE STYLE: UK3042
Connectors Model
2.92mm-F ZXHF-K721M+

Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Temperature stable, up to 105°C
- Protected by US Patent No. 8,392,495 ; 9,705,467, additional patent pending
- Protected by China Patent 201080014266.1
- Protected by Taiwan Patent I581494

Applications

- Aerospace & Defense
- S-band Radar
- GPS

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Stop Band	Rejection	DC-F1	DC - 300	27	35	-	dB
		F1-F2	300 - 450	15	30	-	dB
	Freq. Cut-Off	F3	600	-	3.2	-	dB
	VSWR	DC-F2	DC- 450	-	1.4	-	:1
Pass Band	Insertion Loss	F4-F6	700 - 5000	-	1.9	2.7	dB
		F4-F5	700 - 2000	-	1.1	-	:1
	VSWR	F5-F6	2000 - 5000	-	1.7	-	:1

Absolute Maximum Ratings³

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-55°C to +105°C
RF Power Input, Passband (F4-F6) ¹	32 dBm at 25°C
RF Power Input, Stopband (DC-F4) ²	35 dBm at 25°C

¹ Passband rating derates linearly to 29 dBm at 105°C ambient


² Stopband rating derates linearly to 32 dBm at 105°C ambient

³ Permanent damage may occur if any of these limits are exceeded


ESD rating

Human body model (HBM): Class 2(Pass 2000V) in accordance with ANSI/ESD 5.1-2001

Functional Schematic



Typical Frequency Response





+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	47.02	1.90
10	45.31	1.88
100	30.60	1.60
200	40.21	1.21
250	33.80	1.12
300	33.58	1.17
450	20.56	1.13
480	12.40	1.07
500	8.96	1.03
600	3.17	1.05
700	1.90	1.10
800	1.39	1.10
1000	0.96	1.05
2000	0.72	1.32
2500	0.88	1.53
3000	1.03	1.73
3500	1.20	1.90
4000	1.28	2.03
5000	1.29	2.10
10000	2.29	2.40



Notes

- A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp




www.minicircuits.com P.O. Box 350166, Brooklyn, NY 11235-0003 (718) 934-4500 sales@minicircuits.com

REV. OR
ECO-004934
ZXHF-K721M+
EDU3892
URJ
210118
Page 2 of 3

Coaxial Connections

PORT - 1	2.92mm-Female
PORT - 2	2.92mm-Female

Outline Drawing



Outline Dimensions (inch
mm)

A	B	C	D	E	F
.68	.60	.39	.200	.10	.400
17.1	15.2	10.0	5.08	2.5	10.16
G	H	J	K	Wt.	
.24	.070	.22	.30	grams	
6.0	1.78	5.5	7.6	24	

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp





Coaxial Reflectionless High Pass Filter

ZXHF-K721M+

Typical Performance Data


FREQ.	Insertion Loss	Input Return Loss	Output Return Loss	FREQ.	Group Delay
(MHz)	(dB)	(dB)	(dB)	(MHz)	(ns)
1	47.02	10.18	10.34	700	0.94
5	46.63	10.30	10.34	750	0.78
10	45.31	10.33	10.38	800	0.67
20	41.98	10.46	10.50	850	0.60
30	38.56	10.60	10.64	900	0.54
50	33.69	11.17	11.17	950	0.49
100	30.60	12.74	12.75	1000	0.45
150	35.53	15.67	15.66	1050	0.42
200	40.21	20.57	20.53	1100	0.40
220	37.72	23.03	22.97	1150	0.38
240	34.87	24.84	24.77	1200	0.36
260	33.05	24.76	24.70	1250	0.35
280	32.62	23.39	23.37	1300	0.33
300	33.58	22.03	22.05	1350	0.32
320	35.28	21.25	21.28	1400	0.31
340	35.85	21.12	21.16	1450	0.30
360	33.86	21.56	21.62	1500	0.29
380	31.02	22.45	22.51	1550	0.29
400	29.14	23.30	23.34	1600	0.28
420	27.60	23.51	23.61	1650	0.27
450	20.56	24.32	24.55	1700	0.26
460	17.49	25.41	25.74	1750	0.26
480	12.40	29.47	30.16	1800	0.26
500	8.96	35.30	36.79	1850	0.26
520	6.76	40.44	43.09	1900	0.25
550	4.80	49.25	44.42	1950	0.25
600	3.17	32.22	30.89	2000	0.25
650	2.37	27.79	26.78	2050	0.24
700	1.90	26.04	25.28	2100	0.24
800	1.39	26.12	25.16	2150	0.24
1000	0.96	31.94	30.40	2200	0.24
1500	0.68	24.27	24.22	2250	0.23
2000	0.72	17.14	17.12	2300	0.23
2200	0.77	15.66	15.59	2350	0.23
2400	0.84	14.24	14.20	2400	0.23
2600	0.91	13.11	13.08	2450	0.22
2800	0.97	12.17	12.17	2500	0.22
3000	1.03	11.46	11.48	2550	0.22
3200	1.10	10.94	10.93	2600	0.22
3400	1.18	10.36	10.37	2650	0.22
3600	1.23	9.98	9.96	2700	0.22
3800	1.25	9.57	9.64	2750	0.22
4000	1.28	9.38	9.42	2800	0.22
4200	1.31	9.19	9.26	2850	0.21
4400	1.32	9.07	9.13	2900	0.21
4600	1.32	9.00	9.10	2950	0.21
4800	1.28	8.98	9.08	3000	0.21
5000	1.29	8.98	9.13	3050	0.21
5200	1.26	9.02	9.19	3500	0.20
5400	1.27	9.15	9.32	3600	0.20
5600	1.26	9.23	9.40	3700	0.20
5800	1.25	9.43	9.63	3800	0.20
6000	1.51	9.65	9.94	3900	0.20
6200	1.29	9.32	9.52	4000	0.20
6400	1.28	9.42	9.67	4100	0.20
6600	1.28	9.44	9.69	4200	0.19
7000	1.38	9.37	9.71	4300	0.20
8000	2.18	8.88	9.04	4400	0.19
9000	3.19	9.63	9.48	4500	0.20
10000	2.29	7.72	7.62	5000	0.20

Typical Performance Curves



Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .050$; 3 Pl. $\pm .015$

Notes:

- Case material: Brass alloy.
- Case Finish:
 - Case & Cover of the units –Gold plating.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS



All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet