Coaxial Reflectionless

Low Pass Filter

ZXLF Series

50Ω DC to 11 GHz



The Big Deal

- Patented design terminates Stopband signals
- Stopband up to 35 GHz
- High Stopband rejection, up to 50 dB

Product Overview

Mini-Circuits' ZXLF Series reflectionless filters employs a novel filter topology which absorbs and terminates stop band signals internally rather than reflecting them back to the source. Reflectionless filters eliminate stopband reflections, allowing them to be paired with sensitive devices and used in applications that otherwise require circuits such as isolation amplifiers or attenuators. This is developed in a new broadband, stable connectorized package.

Key Features

Feature	Advantages
Easy integration with sensitive reflective components, e.g. mixers, multipliers	Reflectionless filters absorb unwanted signals, preventing reflections back to the source. This reduces generation of additional unwanted signals without the need for extra components like attenuators, improving system dynamic range.
Cascadable	Reflectionless filters can be cascaded in multiple sections to provide sharper and higher attenuation, while also preventing any standing waves that could affect pass band signals.
Excellent stability over temperature	Minimal variation in electrical performance across temperature.
Operating temperature up to 105˚C	Suitable for operation close to high power components.
Broadband connectorized package	The connectorized package works well even in high frequencies and easy to interface with other devices. This is well suited for test setups.

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Reflectionless

Low Pass Filter

ZXLF-K762+

50Ω DC to 7600 MHz



Generic photo used for illustration purposes only

CASE STYLE: UK3042

Connectors	Model
2.92mm-F	ZXLF-K762+


Features

- Match to 50Ω in the stop band, eliminates undesired reflections
- Cascadable
- Temperature stable, up to 105°C
- Protected by US Patent No. 8,392,495


Applications

- Aerospace & Defense
- Telecomm
- Extended WiFi
- Satellite Comm

Functional Schematic



Typical Frequency Response



+RoHS Compliant

The +Suffix identifies RoHS Compliance. See our web site for RoHS Compliance methodologies and qualifications

Electrical Specifications at 25°C

Parameter		F#	Frequency (MHz)	Min.	Typ.	Max.	Unit
Pass Band	Insertion Loss	DC-F1	DC- 7600	-	1.6	2.8	dB
	Freq. Cut-Off	F2	11000	-	3.5	-	dB
	VSWR	DC-F1	DC- 7600	-	1.3	-	:1
Stop Band	Rejection	F3-F5	13100 - 23000	12	15	-	dB
	VSWR	F3-F4	13100 - 20000	-	1.7	-	:1
		F4-F5	20000 - 23000	-	2.7	-	:1

Absolute Maximum Ratings[3]

Parameter	Ratings
Operating Temperature	-55°C to +105°C
Storage Temperature	-55°C to +105°C
RF Power Input, Passband (DC-F1)[1]	2W at 25°C
RF Power Input, Stopband (F2-F5)[2]	100mW at 25°C


[1] Passband rating derates linearly to 1W at 105°C ambient
[2] Stopband rating derates linearly to 50mW at 105°C ambient
[3] Permanent damage may occur if any of these limits are exceeded


ESD rating

Human body model (HBM): Class 1A (250 to <500V) in accordance with ANSI/ESD 5.1-2001

Typical Performance Data at 25°C

Frequency (MHz)	Insertion Loss (dB)	VSWR (:1)
1	0.35	1.03
10	0.29	1.03
100	0.33	1.02
150	0.38	1.02
200	0.40	1.01
500	0.51	1.04
1000	0.65	1.12
2000	0.88	1.29
7600	1.52	1.18
11000	3.76	1.65
12000	6.55	1.35
13100	15.79	1.08
15000	26.72	1.74
16000	21.87	1.66
17000	19.52	1.66
18000	19.58	1.56
20000	26.80	1.13
21000	23.71	1.69
23000	17.93	3.37
25000	15.95	3.98






Notes

A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Connections

PORT - 1	2.92mm-Female
PORT - 2	2.92mm-Female

Outline Drawing



Outline Dimensions (inch / mm)

A	B	C	D	E	F
.68	**.60**	**.39**	**.200**	**.10**	**.400**
17.1	15.2	10.0	5.08	2.5	10.16

G	H	J	K		Wt.
.24	**.070**	**.22**	**.30**		grams
6.0	1.78	5.5	7.6		**24**

Note: Please refer to case style drawing for details

Notes
A. Performance and quality attributes and conditions not expressly stated in this specification document are intended to be excluded and do not form a part of this specification document.
B. Electrical specifications and performance data contained in this specification document are based on Mini-Circuit's applicable established test performance criteria and measurement instructions.
C. The parts covered by this specification document are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp

Coaxial Reflectionless Low Pass Filter ZXLF-K762+


Typical Performance Data

FREQ. (MHz)	Insertion Loss (dB)	Input Return Loss (dB)	Output Return Loss (dB)
1	0.35	37.20	37.57
5	0.28	37.65	38.03
10	0.29	37.96	38.19
15	0.29	38.28	38.22
25	0.30	38.43	38.55
50	0.25	36.36	36.29
100	0.33	39.12	38.81
150	0.38	41.87	41.62
200	0.40	44.79	43.67
300	0.44	41.88	40.77
350	0.47	38.90	38.62
450	0.50	34.94	34.55
500	0.51	33.33	32.95
550	0.52	31.96	31.74
600	0.55	30.74	30.52
650	0.55	29.71	29.49
700	0.57	28.82	28.56
750	0.59	27.92	27.71
850	0.61	26.57	26.28
900	0.62	25.86	25.54
1000	0.65	24.68	24.42
1100	0.68	23.59	23.36
1150	0.68	23.15	22.93
1500	0.75	20.37	20.20
1600	0.78	19.77	19.65
1700	0.83	19.40	19.28
2000	0.88	17.87	17.71
3000	1.09	15.21	15.12
4000	1.19	14.93	14.89
5000	1.21	16.98	17.05
7000	1.40	24.05	23.44
7600	1.52	21.74	21.01
8000	1.63	19.41	18.88
10000	2.81	11.36	11.58
11000	3.76	12.25	12.68
11500	4.71	14.50	15.15
12000	6.55	16.52	16.93
12500	9.68	19.56	19.04
13000	14.54	38.30	40.75
13100	15.79	28.48	34.84
14000	27.18	12.68	12.76
14500	28.11	11.39	10.88
15000	26.72	11.34	10.44
15500	24.16	11.79	10.86
16000	21.87	12.09	11.82
16500	20.35	12.09	13.06
17000	19.52	12.08	14.31
17500	19.29	12.34	15.44
18000	19.58	13.16	16.43
18500	20.45	14.83	17.47
19000	21.99	18.01	18.98
19500	24.33	24.87	21.69
20000	26.80	24.22	25.00
20100	27.06	22.17	25.04
20200	27.16	20.33	24.48
21000	23.71	11.80	15.71
21500	21.33	9.08	12.05
22000	19.69	7.29	9.56
23000	17.93	5.31	6.64
25000	15.95	4.47	4.69


FREQ. (MHz)	Group Delay (ns)
1	0.21
40	0.20
50	0.20
75	0.20
100	0.20
125	0.19
150	0.19
175	0.19
250	0.19
400	0.19
550	0.19
700	0.19
850	0.19
1000	0.19
1150	0.19
1300	0.19
1450	0.19
1600	0.19
1750	0.18
1900	0.19
2050	0.19
2200	0.19
2350	0.18
2500	0.19
2650	0.19
2800	0.18
2950	0.18
3100	0.19
3250	0.19
3400	0.18
3550	0.18
3700	0.19
3850	0.19
4000	0.19
4150	0.19
4300	0.19
4450	0.19
4600	0.19
4750	0.19
4900	0.19
5050	0.19
5200	0.19
5350	0.19
5500	0.19
5650	0.19
5800	0.19
5950	0.19
6100	0.19
6250	0.19
6400	0.20
6550	0.20
6700	0.20
6850	0.20
7000	0.20
7150	0.20
7300	0.20
7450	0.20
7500	0.20
7550	0.20
7600	0.20

Typical Performance Curves


INSERTION LOSS
INPUT POWER = 0 dBm




INPUT RETURN LOSS
INPUT POWER = 0 dBm



OUTPUT RETURN LOSS
INPUT POWER = 0 dBm




GROUP DELAY
INPUT POWER = 0 dBm



Case Style UK

Outline Dimensions

UK3042



CASE#	A	B	C	D	E	F
UK3042	.68 (17.1)	.60 (15.2)	.39 (10.0)	.200 (5.08)	.10 (2.5)	.400 (10.16)

CASE#	G	H	J	K	WT.GRAMS
UK3042	.24 (6.0)	.070 (1.78)	.22 (5.5)	.30 (7.6)	24

Dimensions are in inches (mm). Tolerances: 2 Pl. ± .050; 3 Pl. ± .015

Notes:

1. Case material: Brass alloy.
2. Case Finish:
   a. Case & Cover of the units –Gold plating.
3. Refer to the individual model data sheet for the type of connectors available.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED
ALL NEW minicircuits.com
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com
RF/IF MICROWAVE COMPONENTS

This document and its contents are the property of Mini-Circuits

Mini-Circuits

Environmental Specifications ENV002

All Mini-Circuits products are manufactured under exacting quality assurance and control standards, and are capable of meeting published specifications after being subjected to any or all of the following physical and environmental test.

Specification	Test/Inspection Condition	Reference/Spec
Operating Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet
Storage Temperature	-55° to 105°C Ambient Environment	Individual Model Data Sheet

This document and its contents are the property of Mini-Circuits.