

dBm - volts - watts conversion

(50-ohm system)

dBm	V	W	dBm	V	mW	dBm	mV	μW	dBm	μV	pW
53	99.9	200	0	0.224	1.00	-49	0.79		-98	2.8	
50	70.7	100	-1	0.199	0.79	-50	0.71	.01 μW	-99	2.51	
49	63.0	79	-2	0.178	0.63	-51	0.63		-100	2.24	.1 pW
48	56.2	63	-3	0.158	0.50	-52	0.56		-101	2.0	
47	50.1	50	-4	0.141	0.40	-53	0.50		-102	1.8	
46	44.6	40	-5	0.126	0.32	-54	0.45		-103	1.6	
45	39.8	32	-6	0.112	0.25	-55	0.40		-104	1.41	
44	35.4	25	-7	0.100	0.20	-56	0.35		-105	1.26	
43	31.6	20	-8	0.089	0.16	-57	0.32		-106	1.12	
42	28.2	16	-9	0.079	0.126	-58	0.282		dBm	nV	
41	25.1	12.6	-10	0.071	0.10	-59	0.251		-107	999	
40	22.4	10	-11	0.063		-60	0.224	.001 μW	-108	890	
39	19.9	8.0	-12	0.056		-61	0.199		-109	793	
38	17.8	6.3	-13	0.050		-62	0.178		-110	707	.01pW
37	15.8	5.0	-14	0.045		-63	0.158		-111	630	
36	14.1	4.0	-15	0.040		-64	0.141		-112	562	
35	12.6	3.2	-16	0.0354		dBm	uV		-113	501	
34	11.2	2.5	dBm	mV		-65	126		-114	446	
33	10.0	2.0	-17	31.6		-66	112		-115	398	
32	8.9	1.6	-18	28.2		-67	100		-116	354	
31	7.9	1.26	-19	25.1		-68	89		-117	316	
30	7.07	1.0	-20	22.4	.01 mW	-69	79		-118	282	
dBm	V	mW	-21	19.9		70	71	.1nW	-119	251	
29	6.30	794	-22	17.8		-71	63		-120	224	.001pW
28	5.62	631	-23	15.8		-72	56		-121	199	
27	5.01	501	-24	14.1		-73	50		-122	178	
26	4.46	398	-25	12.6		-74	45		-123	158	
25	3.98	316	-26	11.2		-75	40		-124	141	
24	3.54	251	-27	10.0		-76	35		-125	126	
23	3.16	200	-28	8.9		-77	32		-126	112	
22	2.82	158	-29	7.9		-78	28		-127	100	
21	2.51	126	-30	7.1	.001mW	-79	25		-128	89	
20	2.24	100	-31	6.30		-80	22.4	.01 nW	-129	79	
19	1.99	79	-32	5.6		-81	19.9		-130	71	.1fW
18	1.78	63	-33	5.0		-82	17.8		-131	63	
17	1.58	50	-34	4.5		-83	15.8		-132	56	
16	1.41	40	-35	4.0		-84	14.1		-133	50	
15	1.26	32	-36	3.5		-85	12.6		-134	45	
14	1.12	25	-37	3.2		-86	11.2		-135	40	
13	1.00	20	-38	2.82		-87	10.0		-136	35	
12	.89	16	-39	2.5		-88	8.9		-137	32	
11	.79	12.6	-40	2.24	.1μW	-89	7.9		-138	28	
10	.71	10	-41	2.0		-90	7.1	.001 nW	-139	25	
9	.63	8.0	-42	1.8		-91	6.3		-140	22	.01fW
8	.56	6.3	-43	1.6		-92	5.62				
7	.501	5.0	-44	1.4		-93	5.0				
6	.446	4.0	-45	1.26		-94	4.5				
5	.398	3.2	-46	1.12		-95	4.0				
4	.354	2.5	-47	1.00		-96	3.54				
3	.316	2.0	-48	0.89		-97	3.2				
2	.282	1.6									
1	.251	1.26									



ISO 9001 ISO 14001 AS 9100 CERTIFIED

The Design Engineers Search Engine



Provides ACTUAL Data Instantly at minicircuits.com

IFIRF MICROWAVE COMPONENTS

For detailed performance specs & shopping online see web site

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.

IMPORTANT NOTICE

© 2015 Mini-Circuits

This document is provided as an accommodation to Mini-Circuits customers in connection with Mini-Circuits parts only. In that regard, this document is for informational and guideline purposes only. Mini-Circuits assumes no responsibility for errors or omissions in this document or for any information contained herein.

Mini-Circuits may change this document or the Mini-Circuits parts referenced herein (collectively, the "Materials") from time to time, without notice. Mini-Circuits makes no commitment to update or correct any of the Materials, and Mini-Circuits shall have no responsibility whatsoever on account of any updates or corrections to the Materials or Mini-Circuits' failure to do so.

Mini-Circuits customers are solely responsible for the products, systems, and applications in which Mini-Circuits parts are incorporated or used. In that regard, customers are responsible for consulting with their own engineers and other appropriate professionals who are familiar with the specific products and systems into which Mini-Circuits' parts are to be incorporated or used so that the proper selection, installation/integration, use and safeguards are made. Accordingly, Mini-Circuits assumes no liability therefor.

In addition, your use of this document and the information contained herein is subject to Mini-Circuits' standard terms of use, which are available at Mini-Circuits' website at www.minicircuits.com/homepage/terms_of_use.html.

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation: (i) by Mini-Circuits of such third-party's products, services, processes, or other information; or (ii) by any such third-party of Mini-Circuits or its products, services, processes, or other information.


ISO 9001 ISO 14001 AS 9100 CERTIFIED
P.O. Box 350166, Brooklyn, New York 11235-0003 (7 18) 934-4500 Fax (7 18) 332-4661 The Design Engineers Search Engine  Provides ACTUAL Data Instantly at minicircuits.com
IFIRF MICROWAVE COMPONENTS 

For detailed performance specs & shopping online see web site

Notes: 1. Performance and quality attributes and conditions not expressly stated in this specification sheet are intended to be excluded and do not form a part of this specification sheet. 2. Electrical specifications and performance data contained herein are based on Mini-Circuit's applicable established test performance criteria and measurement instructions. 3. The parts covered by this specification sheet are subject to Mini-Circuits standard limited warranty and terms and conditions (collectively, "Standard Terms"); Purchasers of this part are entitled to the rights and benefits contained therein. For a full statement of the Standard Terms and the exclusive rights and remedies thereunder, please visit Mini-Circuits' website at www.minicircuits.com/MCLStore/terms.jsp.