

## APPLICATION NOTE AN-60-107


### ZPUL-30P+ vs ZPUL-30P

**The new Catalog model ZPUL-30P+ designed to replace the old one ZPUL-30P due to the RoHS version and EOL of the output transistor. Case Style S32 is not changed**

#### Typical Performance Data

FREQUENCY (MHz)	GAIN (dB)		DIRECTIVITY (dB)		VSWR (:1)				NOISE FIGURE (dB)		POUT @ 1 dB COMPRESSION (dBm)		OUTPUT IP3 (dBm)	
	NEW 24V	OLD 24V	NEW 24V	OLD 24V	IN (NEW) 24V	OUT (NEW) 24V	IN (OLD) 24V	OUT (OLD) 24V	NEW 24V	OLD 24V	NEW 24V	OLD 24V	NEW 24V	OLD 24V
0.0025	35.6	35.7	31.2	31.30	1.33	1.23	1.18	2.90						-
0.01	35.1	35.6	25.9	24.83	1.08	1.08	1.06	2.85						-
0.05	35.0	35.5	28.0	30.45	1.06	1.06	1.02	3.05						-
0.10	35.0	35.4	22.4	32.68	1.02	1.05	1.02	3.10						-
0.20	35.1	35.4	24.6	38.52	1.02	1.10	1.01	3.10						-
1.00	35.2	35.5	28.0	43.08	1.02	1.15	1.01	3.18						-
2.00	35.1	36.0	27.6	41.90	1.03	1.15	1.04	3.17						-
10.00	34.6	36.8	47.0	36.43	1.03	1.17	1.05	2.60	8.04	7.23	22.7	27.1	37.9	-
50.00	34.6	37.0	45.8	37.37	1.06	1.19	1.04	1.45	7.79	7.24	25.5	25.3	38.0	-
100.00	35.1	37.0	51.3	43.92	1.08	1.23	1.06	1.36	7.81	7.23	25.5	25.3	37.4	-
200.00	35.5	37.0	44.6	38.72	1.08	1.31	1.11	1.41	7.82	7.21	25.0	25.0	37.4	-
300.00	35.5	37.0	39.1	37.33	1.08	1.35	1.17	1.53	7.81	7.20	24.5	24.7	36.4	-
400.00	35.3	36.9	49.0	44.85	1.09	1.31	1.27	1.61	7.82	7.16	24.0	24.2	36.8	-
500.00	35.1	36.1	40.3	33.38	1.12	1.22	1.35	1.65	7.82	7.20	23.8	23.2	36.2	-
600.00	35.0	36.0	40.8	34.50	1.16	1.20	1.47	1.72	7.85	7.29	23.7	22.0	35.3	-
700.00	35.1	35.6	58.6	35.00	1.23	1.44	1.52	1.98	7.86	7.24	22.7	21.0	33.9	-

#### Typical performance graphs



### IMPORTANT NOTICE

© 2015 Mini-Circuits

This document is provided as an accommodation to Mini-Circuits customers in connection with Mini-Circuits parts only. In that regard, this document is for informational and guideline purposes only. Mini-Circuits assumes no responsibility for errors or omissions in this document or for any information contained herein.

Mini-Circuits may change this document or the Mini-Circuits parts referenced herein (collectively, the "Materials") from time to time, without notice. Mini-Circuits makes no commitment to update or correct any of the Materials, and Mini-Circuits shall have no responsibility whatsoever on account of any updates or corrections to the Materials or Mini-Circuits' failure to do so. Mini-Circuits customers are solely responsible for the products, systems, and applications in which Mini-Circuits parts are incorporated or used. In that regard, customers are responsible for consulting with their own engineers and other appropriate professionals who are familiar with the specific products and systems into which Mini-Circuits' parts are to be incorporated or used so that the proper selection, installation/integration, use and safeguards are made. Accordingly, Mini-Circuits assumes no liability therefore.

In addition, your use of this document and the information contained herein is subject to Mini-Circuits' standard terms of use, which are available at Mini-Circuits' website at [www.minicircuits.com/homepage/terms\\_of\\_use.html](http://www.minicircuits.com/homepage/terms_of_use.html).

Mini-Circuits and the Mini-Circuits logo are registered trademarks of Scientific Components Corporation d/b/a Mini-Circuits. All other third-party trademarks are the property of their respective owners. A reference to any third-party trademark does not constitute or imply any endorsement, affiliation, sponsorship, or recommendation: (i) by Mini-Circuits of such third-party's products, services, processes, or other information; or (ii) by any such third-party of Mini-Circuits or its products, services, processes, or other information.