


Outline Dimensions

AH1596



Suggested Layout,
Tolerance to be within $\pm .002$

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
AH1596	.50 (12.70)	.62 (15.75)	.36 (9.14)	- -	.115 (2.92)	.070 (1.78)	.073 (1.85)	- -	.090 (9.65)	.040 (1.02)	.037 (0.94)	.140 (3.56)	.135 (3.43)

CASE #	P	Q	R	WT, GRAM
AH1596	.010 (0.25)	- -	.135 (3.43)	3.00

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .01$; 3 Pl. $\pm .005$

Notes:

- Open style, Base material: Printed wiring laminate.
- Termination finish: 3-5 μ inch (.08-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS