





Case Style

AT3278




3D views for reference only


TOP VIEW






BOTTOM VIEW



PCB LAND PATTERN



**SUGGESTED LAYOUT
TOLERANCE TO BE WITHIN: ± 0.002**



Refer to individual units for wiring information

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	WT. GRAMS
AT3278	.146 (3.71)	.235 (5.97)	.145 (3.68)	.084 (2.13)	.032 (0.81)	.034 (0.86)	.034 (0.86)	.062 (1.58)	.111 (2.81)	.042 (1.07)	.038 (0.97)	.084 (2.13)	.111 (2.82)	.210 (5.33)	.146 (3.71)	.009 (0.23)	.15
Dimensions are in inches (mm). Tolerances: 3 Pl. $\pm .004$										See tolerances in views							



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS

