


## Outline Dimensions

AW256



| CASE # | A                | B               | C               | D              | E                 | F                | G              | H               | J              | K               | WT. GRAM |
|--------|------------------|-----------------|-----------------|----------------|-------------------|------------------|----------------|-----------------|----------------|-----------------|----------|
| AW256  | 4.50<br>(114.30) | 2.25<br>(57.15) | 1.69<br>(42.93) | .125<br>(3.18) | 4.000<br>(101.60) | 1.625<br>(41.28) | .144<br>(3.66) | .890<br>(22.61) | .44<br>(11.18) | 3.50<br>(88.90) | 500      |

Dimensions are in inches (mm). Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

### Notes:

- Case material: Aluminum alloy.
- Case Finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Heat sink finish: Black anodize.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS