


Case Style

Outline Dimensions

BT

BT3258



MOUNTING INFORMATION FOR MODELS WITHOUT HEATSINK

CASE#	A	B	C	D	E	F	G	H	J	K	L	M	N
BT3258	9.85 (250.19)	7.3 (185.0)	6.62 (168.1)	5.91 (150.0)	.98 (24.89)	3.75 (95.25)	.13 (3.18)	.90 (22.76)	.72 (18.25)	1.61 (40.9)	.59 (15.00)	.68 (17.20)	.57 (14.50)
CASE #	P	Q	R	S	T	U	WT, GRAM	WT WITHOUT HEATSINK, GRAM					
BT3258	5.91 (150.00)	2.05 (52.07)	9.06 (230.00)	1.18 (30.00)	.135 (3.43)	.57 (14.50)	5350	1820					

Dimensions are in inches (mm). Tolerances: 2 Pl.±.03; 2 Pl.±.015;

Notes:

- Case material: Aluminum alloy.
- Finish:
For RoHS Case Styles: Clear Chemical conversion coating, non-chrome or trivalent chrome based
- Heatsink finish: Black anodize.
- Refer to the individual model data sheet for the type of connectors available.
- Recommended screw for mounting model without heatsink on 3/32" thick sheet: #6-32, 1.50" Length.

Mini-Circuits
ISO 9001 ISO 14001 CERTIFIED

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site
The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com



ALL NEW
minicircuits.com