




Outline Dimensions

CH513
CH549



Suggested Layout,
Tolerance to be within ± 0.002

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
CH513	.500 (12.70)	.500 (12.70)	.200 (5.08)	.100 (2.54)	.185 (4.70)	.220 (5.59)	.060 (1.52)	.070 (1.78)	.510 (12.95)	.065 (1.65)	.190 (4.83)	.225 (5.72)	.117 (2.97)
CH549			.170 (4.32)										

CASE #	P	Q	R	S	T	WT. GRAM
CH513	.123 (3.12)	.220 (5.59)	.215 (5.46)	.110 (2.79)	.130 (3.30)	1.0
CH549						.85

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Nickel-Silver alloy.
- Header: Printed wiring laminate.
- Termination finish:

For For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.

For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified