



Outline Dimensions



PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm .002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M	N
DL1636	.236 (6.00)	.193 (4.90)	.035 (0.90)	.008 (0.20)	.160 (4.05)	.153 (3.89)	.017 (0.42)	-- --	.024 (0.60)	.050 (1.27)	.162 (4.11)	.040 (1.02)	.020 (0.51)

CASE #	P	Q	R	S	T	WT. GRAM
DL1636	.257 (6.53)	.011 (0.28)	.155 (3.94)	.020 (0.51)	.050 (1.27)	.08

Dimensions are in inches (mm). Tolerances: 3Pl. $\pm .004$, unless otherwise specified.

Notes:

1. Case material: Plastic.
2. Termination finish:

For RoHS Case Styles: Tin-Silver-Nickel plate or Matte-Tin. All models, (+) suffix. See model data sheet.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS