


### Outline Dimensions



\* OVERALL CONNECTOR OR CABLE & BOOT DIM  
[CONNECTOR SHAPE MAY VARY]

GM1526 SERIES  
QUICK LOCK SMA MALE (CONN-1)  
SMA MALE (CONN-2)

| CASE STYLE # | A     |        | B              | C | D             | E              | T        |           | WEIGHT<br>GRAMS |
|--------------|-------|--------|----------------|---|---------------|----------------|----------|-----------|-----------------|
|              | FEET  | METERS |                |   |               |                | INCHES   | MM        |                 |
| GM1526-.67   | .67   | .20    | .43<br>(10.92) | - | .36<br>(9.14) | .312<br>(7.92) | +.50/-0  | +12.7/-0  | 22              |
| GM1526-1.0   | 1.00  | .30    |                |   |               |                | +.50/-0  | +12.7/-0  | 26              |
| GM1526-1.5   | 1.50  | .46    |                |   |               |                | +.50/-0  | +12.7/-0  | 33              |
| GM1526-1.64  | 1.64  | .50    |                |   |               |                | +.50/-0  | +12.7/-0  | 35              |
| GM1526-2     | 2.00  | .61    |                |   |               |                | +.50/-0  | +12.7/-0  | 40              |
| GM1526-3     | 3.00  | .91    |                |   |               |                | +.72/-0  | +18.3/-0  | 53              |
| GM1526-3.28  | 3.28  | 1.00   |                |   |               |                | +.79/-0  | +20.0/-0  | 57              |
| GM1526-4     | 4.00  | 1.22   |                |   |               |                | +.96/-0  | +24.4/-0  | 67              |
| GM1526-5     | 5.00  | 1.52   |                |   |               |                | +1.20/-0 | +30.5/-0  | 81              |
| GM1526-6     | 6.00  | 1.83   |                |   |               |                | +1.44/-0 | +36.6/-0  | 94              |
| GM1526-6.56  | 6.56  | 2.00   |                |   |               |                | +1.57/-0 | +40.0/-0  | 102             |
| GM1526-18    | 18.00 | 5.49   |                |   |               |                | +4.32/-0 | +109.7/-0 | 257             |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl.  $\pm .03$ ; 3Pl.  $\pm .015$

#### Note:

1. Flexible Coaxial Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified