


Outline Dimensions



KQ1506 SERIES
 SMA MALE (CONN-1)
 SMA MALE (CONN-2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WEIGHT GRAMS
	INCH	MM							141U-ASM+	141-ASM+	INCH	MM	
KQ1506-2	2.00	50.80	.36 (9.14)	.315 (8.00)	.250 (6.35)	.36 (9.14)	.315 (8.00)	.250 (6.35)	.141±.003 (3.58±0.07)	.163±.004 (4.14±0.10)	.05	1.27	6.89
KQ1506-3	3.00	76.20									.05	1.27	8.03
KQ1506-3.94	3.94	100.00									.05	1.27	9.10
KQ1506-4	4.00	101.60									.05	1.27	9.17
KQ1506-5	5.00	127.00									.05	1.27	10.32
KQ1506-6	6.00	152.40									.05	1.27	11.46
KQ1506-7	7.00	177.80									.10	2.54	12.60
KQ1506-7.87	7.87	200.00									.10	2.54	13.60
KQ1506-8	8.00	203.20									.10	2.54	13.74
KQ1506-9	9.00	228.60									.10	2.54	14.89
KQ1506-10	10.00	254.00							.10	2.54	16.03		
KQ1506-11	11.00	279.40							.10	2.54	17.17		
KQ1506-11.81	11.81	300.00							.10	2.54	18.09		
KQ1506-12	12.00	304.80							.10	2.54	18.32		
KQ1506-13	13.00	330.20							.15	3.81	19.46		
KQ1506-14	14.00	355.60							.15	3.81	20.60		
KQ1506-15	15.00	381.00							.15	3.81	21.75		
KQ1506-16	16.00	406.40							.15	3.81	22.89		
KQ1506-17	17.00	431.80							.15	3.81	24.03		
KQ1506-18	18.00	457.20							.15	3.81	25.17		
KQ1506-19	19.00	482.60	.15	3.81	26.32								
KQ1506-19.7	19.69	500.00	.15	3.81	27.12								
KQ1506-20	20.00	508.00	.15	3.81	27.45								

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. 141 Hand-Flex™ Coaxial Cable.
2. "A" Represents Length of Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified

Outline Dimensions

KQ1506 SERIES
SMA MALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WEIGHT GRAMS								
	INCH	MM							141U-ASM+	141-ASM+	INCH	MM									
KQ1506-22	22.00	558.80	.36 (9.14)	.315 (8.00)	.250 (6.35)	.36 (9.14)	.315 (8.00)	.250 (6.35)	.141±.003 (3.58±0.07)	.163±.004 (4.14±0.10)	.15	3.81	29.75								
KQ1506-24	24.00	609.60									.15	3.81	32.03								
KQ1506-26	26.00	660.40									.20	5.08	34.32								
KQ1506-30	30.00	762.00									.20	5.08	38.89								
KQ1506-32	32.00	812.80									.20	5.08	41.18								
KQ1506-36	36.00	914.40									.30	7.62	45.75								
KQ1506-39.4	39.37	1000.00									.30	7.62	49.63								
KQ1506-40	40.00	1016.00									.30	7.62	50.32								
KQ1506-48	48.00	1219.20									.40	10.16	61.75								
KQ1506-50	50.00	1270.00									.40	10.16	72.15								
KQ1506-59.1	59.06	1500.00									.40	10.16	73.18								
KQ1506-60	60.00	1524.00									.40	10.16	73.18								
KQ1506-72	72.00	1828.80									.40	10.16	86.90								
KQ1506-78.7	78.74	2000.00									.40	10.16	94.55								

Unless otherwise specified dimensions are in inches (mm).
Tolerances: 2Pl. ± .03; 3Pl. ± .015



INTERNET <http://www.minicircuits.com>
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661
Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010
Mini-Circuits ISO 9001 & ISO 14001 Certified