


Outline Dimensions



CUT OUT FOR SMA FEMALE BULKHEAD CONNECTOR
PANEL THICKNESS .100 MAX INCHES

KQ1688 SERIES
SMA FEMALE BULKHEAD (CONN-1)
SMA MALE (CONN-2)

| CASE STYLE # | A | | B | C1 | C2 | D | E1 | E2 | F | | T | | WEIGHT GRAMS |
|--------------|-------|--------|----------------|-----------------|----------------|---------------|----------------|----------------|--------------------------|--------------------------|------|------|--------------|
| | INCH | MM | | | | | | | 141U-ASBSM+ | 141-ASBSM+ | INCH | MM | |
| KQ1688-4 | 4.00 | 101.60 | .51 (12.95) | .438 (11.13) | .232 (5.89) | .36 (9.14) | .313 (7.95) | .250 (6.35) | .141±.003 (3.58±0.07) | .163±.004 (4.14±0.10) | .05 | 1.27 | 10.17 |
| KQ1688-7 | 7.00 | 177.80 | | | | | | | | | .10 | 2.54 | 13.60 |
| KQ1688-12 | 12.00 | 304.80 | | | | | | | | | .10 | 2.54 | 19.32 |
| KQ1688-24 | 24.00 | 609.60 | | | | | | | | | .15 | 3.81 | 33.03 |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |
| | | | | | | | | | | | | | |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

- 141 Hand-Flex™ Coaxial Cable.
- "A" represents length of cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified