


Case Style

LJ


Outline Dimensions

LJ1577


Top View





Front View



Rear View



Bracket Option



CASE#	A	B	C	D	E	F	G	H	J	K	L	WT. GRAMS
LJ1577	6.16 (156.5)	3.68 (93.4)	1.38 (35.0)	.15 (3.8)	.500 (12.7)	4.000 (101.6)	.250 (6.4)	2.250 (57.2)	1.96 (49.7)	.144 (3.7)	.160 (4.1)	300

Dimensions are in inches (mm). Tolerances: 2PL. +/- .03; 3PL. +/- .015

Notes:

- Case material: Plastic.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified