



Outline Dimensions

NL1008C-4




PCB Land Pattern



Suggested Layout,
Tolerance to be within $\pm.002$

NOTES:

- PIN NUMBERS DO NOT APPEAR ON UNIT. FOR REFERENCE ONLY.
-  METALLIZATION
- PAD TOLERANCE IS NON-CUMULATIVE.

CASE #	A	B	C	D	E	F	G	H	J	K	M	WT. GRAM
NL1008C-4	.098 (2.50)	.079 (2.00)	.039 (.99)	.020 (.49)	.010 (.25)	.008 (.20)	.020 (.49)	.012 (.30)	.016 (.41)	.095 (2.41)	-- --	.019

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm.01$; 3 Pl. $\pm.005$

Notes:

- Open style, ceramic base.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate. All models, (+) suffix.
For RoHS-5 Case Styles: Tin-Lead plate. All models, no (+) suffix.
- Line width should be designed to match 50Ω characteristic depending on PCB material and thickness.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS