


Outline Dimensions

RN2486



| CASE # | A | B | C | D | E | F | G | H | J | K | L | M |
|--------|-----------------|----------------|----------------|------------------|-----------------|---------------|---------------|----------------|----------------|---------------|---------------|----------------|
| RN2486 | 1.30 (33.02) | .98 (24.89) | .56 (14.22) | 1.160 (29.46) | .790 (20.07) | .07 (1.78) | .09 (2.29) | .098 (2.49) | .64 (16.26) | .36 (9.14) | .24 (6.10) | .59 (14.99) |

| CASE # | N | P | Q | R | S | T | WT. GRAM |
|--------|----------------|---------------|---------------|----|----|----|----------|
| RN2486 | .42 (10.67) | .21 (5.33) | .39 (9.91) | -- | -- | -- | 74 |

Dimensions are in inches (mm). Tolerances: 2Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

1. Case material: Brass alloy.
2. Case finish: Gold Plating.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

R/F/I/F MICROWAVE COMPONENTS