


Case Style

RZ

Outline Dimensions

RZ2511



| CASE# | A | B | C | D | E | F | G | H | J | K | L | M |
|--------|-----------------|-----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|----------------|
| RZ2511 | .750 (19.05) | .551 (14.00) | .175 (4.45) | .139 (3.52) | .158 (4.00) | .215 (5.46) | .176 (4.48) | .218 (5.52) | .100 (2.54) | .060 (1.52) | .070 (1.78) | .150 (3.81) |

| CASE# | N | P | Q | R | S | T | U | V | WT.GRAMS |
|--------|----------------|----------------|----------------|-----------------|-----------------|-----------------|----------------|-----------------|----------|
| RZ2511 | .238 (6.03) | .215 (5.46) | .159 (4.03) | .431 (10.95) | .630 (16.00) | .790 (20.07) | .080 (2.03) | .591 (15.02) | 2.0 |

Dimensions are in inches (mm). Tolerances: 2PL. ± .03; 3PL. ± .015

Notes:

1. Case material: Nickel-Silver alloy.
2. Base: Printed wiring laminate.
3. Termination finish:
For RoHS Case Styles: 2-5 μ inch (.05-.13 microns) Gold over 120-240 μ inch (3.05-6.10 microns) Nickel plate.
All models, (+) suffix.

Mini-Circuits®
ISO 9001 ISO 14001 CERTIFIED

ALL NEW
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RFIIF MICROWAVE COMPONENTS