


## Outline Dimensions

SC0202C



CASE#	A	B	C	D	E	F	G	H	J	K	L	M	WT. GRAMS
SC0202C	.026 (0.65)	.020 (0.50)	.015 (0.37)	.006 (0.15)	.009 (0.225)	.008 (0.20)	.008 (0.20)	.028 (0.70)	.021 (0.54)	.007 (0.18)	.010 (0.25)	.007 (0.18)	.0005

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .01$ ; 3 Pl.  $\pm .002$

### Notes:

1. Open style, ceramic base.
2. Termination finish:  
For RoHS Case Styles: Matte Tin over Nickel plating. Models with (+) suffix.
3. \*Line width should be designed to match 50 $\Omega$  characteristic impedance, depending on PCB material and thickness



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS