


Case Style


SM18

SM18

Outline Dimensions



PCB Land Pattern



Suggested Layout,

Tolerance to be within $\pm .002$

Each ground pin shall have footprint
Per view "A". All ground pads shall be
connected to each other per view "B"

CASE #.	A	B	C	D	E	F	G	H	J	K	L	M	N	P	Q	R	WT, GRAM
SM18	.375 (9.53)	.510 (12.95)	.095 (2.41)	.425 (10.80)	.100 (2.54)	.015 (.38)	.100 (2.54)	.060 (1.52)	.040 (1.02)	.100 (2.54)	.460 (11.68)	.140 (3.56)	.180 (4.57)	-- --	-- --	.020 (.51)	.4

Dimensions are in inches (mm). Tolerances: $\pm .005$

Notes:

- Case material: Plastic encapsulation on Ceramic base.
- Termination finish:
For RoHS Case Styles: Tin plate over Nickel plate.
For RoHS-5 Case Styles: Tin-Lead plate.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified