


Outline Dimensions

TJ2826-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
TJ2826-1	.472 (12.00)	.394 (10.00)	.110 (2.79)	.060 (1.52)	.322 (8.19)	.075 (1.91)	.244 (6.19)	.160 (4.06)	.157 (4.00)	.317 (8.06)	.095 (2.41)	.120 (3.05)

CASE#	N	P	Q	R	S	T	U	V	W	X	Y	WT.GRAM
TJ2826-1	.137 (3.48)	.257 (6.52)	.055 (1.40)	.115 (2.92)	.204 (5.17)	.274 (6.95)	.434 (11.02)	.080 (2.03)	.352 (8.95)	.282 (7.17)	.512 (13.01)	6

Dimensions are in inches (mm). Tolerances: 2Pl. ± .03; 3Pl. ± .015

Notes:

- Case material: Nickel-Silver alloy.
- Base: Printed wiring laminate.
- Termination finish:
 - For RoHS Case Styles: 3-5μinch (.08-.13microns) Gold over 120-240μinch (3.05-6.10microns) Nickel plate.
 - For RoHS-5 Case Styles: Tin-Lead plate.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS