


## Outline Dimensions

UU640-2



| CASE#   | A                | B               | C              | D                 | E                | F              | G             | H               | J             | K             | L              | M               |
|---------|------------------|-----------------|----------------|-------------------|------------------|----------------|---------------|-----------------|---------------|---------------|----------------|-----------------|
| UU640-2 | 8.27<br>(210.00) | 1.42<br>(36.00) | .50<br>(12.70) | 7.953<br>(202.00) | 4.13<br>(105.00) | .157<br>(4.00) | .43<br>(11.0) | .945<br>(24.00) | .10<br>(2.60) | .27<br>(6.75) | .52<br>(13.10) | .394<br>(10.00) |

| CASE#   | N             | WT. GRAMS |
|---------|---------------|-----------|
| UU640-2 | .236<br>(6.0) | 350       |

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm$  .03; 3 Pl.  $\pm$  .015

### Notes:

- Case material: Aluminum alloy.
- Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.

**Mini-Circuits®**  
ISO 9001 ISO 14001 CERTIFIED

ALL NEW  
minicircuits.com

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS