


Outline Dimensions

VVV2609



CASE#	A	B	C	D	E	F	G	H	J	K	L
VVV2609	3.25 (82.55)	2.46 (62.48)	.75 (19.05)	.75 (19.05)	1.750 (44.45)	.11 (2.79)	Ø.129 (Ø3.28)	2.250 (57.15)	.38 (9.65)	.61 (15.49)	1.250 (31.75)

CASE#	M	WT.GRAMS
VVV2609	1.23 (31.24)	280

Dimensions are in inches (mm). Tolerances: 2 Pl. $\pm .03$; 3 Pl. $\pm .015$

Notes:

- Case material: Aluminum alloy.
- Case finish:
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
- Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From Mini-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS