

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMP-FEMALE 1 RETURN LOSS (dB)	SMP-FEMALE 2 RETURN LOSS (dB)
100	0.03	40.2	39.9
200	0.05	34.0	33.8
300	0.06	30.5	30.3
400	0.07	28.4	28.2
500	0.08	27.0	26.9
600	0.09	26.1	26.1
700	0.10	25.8	25.7
800	0.10	25.8	25.9
900	0.12	26.3	26.3
1000	0.12	27.1	27.2
1100	0.12	28.5	28.6
1200	0.13	30.7	30.6
1300	0.13	33.8	33.4
1400	0.12	38.8	37.2
1500	0.13	43.2	39.5
1600	0.13	38.1	36.8
1800	0.15	31.0	31.1
2000	0.14	28.0	28.3
2500	0.16	27.0	26.4
3000	0.20	31.6	28.8
3500	0.20	34.5	35.8
4000	0.21	25.3	24.2
4500	0.22	25.8	23.9
5000	0.24	41.1	39.1
5500	0.26	25.6	24.5
6000	0.24	25.3	24.4
6500	0.27	35.2	34.0
7000	0.29	27.0	26.8
7500	0.27	26.6	27.3
8000	0.29	32.8	30.9
8500	0.31	31.0	30.7
9000	0.31	27.4	34.4
9500	0.35	28.2	32.0
10000	0.32	32.5	32.0
10500	0.36	30.2	39.8
11000	0.31	23.7	30.8
11500	0.36	23.8	26.0
12000	0.39	30.2	27.4
12500	0.46	23.8	30.2
13000	0.29	22.0	25.6
13500	0.44	27.6	26.1
14000	0.45	23.5	40.1
14500	0.34	21.0	24.5
15000	0.36	27.2	25.9
15500	0.45	26.6	31.1
16000	0.50	26.5	23.7
16500	0.38	38.4	34.1
17000	0.35	26.0	21.9
17500	0.44	24.7	24.5
18000	0.26	19.3	25.0