

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.07	31.4	31.3
200.0	0.10	29.3	29.0
300.0	0.12	33.1	32.6
500.0	0.16	33.7	32.3
600.0	0.18	30.9	30.0
700.0	0.19	33.2	32.5
900.0	0.22	35.8	34.3
1000.0	0.23	32.4	31.2
1100.0	0.25	35.9	33.8
1250.0	0.25	35.8	34.8
1500.0	0.28	35.0	33.3
1750.0	0.30	31.5	31.4
2000.0	0.33	34.2	34.8
2001.0	0.33	34.2	34.8
2250.0	0.35	32.5	30.3
2500.0	0.37	28.9	29.5
2750.0	0.39	31.8	31.3
3000.0	0.40	32.1	29.7
3250.0	0.42	28.1	28.3
3500.0	0.44	28.5	27.8
3750.0	0.45	31.2	28.7
4000.0	0.48	26.3	26.5
4250.0	0.50	29.7	29.2
4500.0	0.51	27.3	26.6
5000.0	0.52	34.8	31.5
5500.0	0.52	32.7	32.6
6000.0	0.54	29.6	29.2
6500.0	0.58	34.5	33.9
7000.0	0.58	32.3	32.1
7500.0	0.62	34.7	32.7
8000.0	0.63	39.9	46.2
8500.0	0.66	35.0	35.3
9000.0	0.68	33.5	34.0
9500.0	0.66	28.1	27.4
10000.0	0.69	24.4	28.5
10500.0	0.71	27.7	29.8
11000.0	0.74	33.0	26.9
11500.0	0.74	21.0	21.5
12000.0	0.64	20.9	20.2
12500.0	0.70	36.7	23.4
13000.0	0.62	24.0	24.1
13500.0	0.61	19.2	19.4
14000.0	0.69	22.5	22.3
14500.0	0.67	29.6	31.4
15000.0	0.80	21.8	23.0
15500.0	0.87	22.6	25.3
16000.0	0.90	26.2	25.4
16500.0	0.94	25.0	29.7
17000.0	1.06	18.8	17.8
17500.0	1.02	23.4	21.8
18000.0	1.03	24.3	23.3