

# Handflex Cable, MCX RA to N Female Bulkhead, 12"

086-12MCRNB+

## Typical Performance Data

| FREQ. | INSERTION LOSS | Right Angle MCX<br>VSWR | N Female Bulkhead<br>VSWR |
|-------|----------------|-------------------------|---------------------------|
| (GHz) | (dB)           | (:1)                    | (:1)                      |
| 0.10  | -0.06          | 1.03                    | 1.03                      |
| 0.20  | -0.10          | 1.03                    | 1.03                      |
| 0.40  | -0.14          | 1.01                    | 1.01                      |
| 0.60  | -0.18          | 1.03                    | 1.05                      |
| 0.80  | -0.20          | 1.02                    | 1.02                      |
| 1.00  | -0.23          | 1.05                    | 1.06                      |
| 1.20  | -0.23          | 1.02                    | 1.05                      |
| 1.40  | -0.21          | 1.07                    | 1.05                      |
| 1.60  | -0.23          | 1.03                    | 1.08                      |
| 1.80  | -0.30          | 1.06                    | 1.06                      |
| 2.00  | -0.34          | 1.06                    | 1.09                      |
| 2.20  | -0.36          | 1.05                    | 1.07                      |
| 2.40  | -0.39          | 1.09                    | 1.10                      |
| 2.60  | -0.40          | 1.06                    | 1.09                      |
| 2.80  | -0.43          | 1.09                    | 1.10                      |
| 3.00  | -0.44          | 1.08                    | 1.11                      |
| 3.20  | -0.46          | 1.08                    | 1.09                      |
| 3.40  | -0.49          | 1.13                    | 1.14                      |
| 3.60  | -0.50          | 1.07                    | 1.09                      |
| 3.80  | -0.52          | 1.14                    | 1.15                      |
| 4.00  | -0.53          | 1.08                    | 1.11                      |
| 4.20  | -0.55          | 1.13                    | 1.14                      |
| 4.40  | -0.57          | 1.12                    | 1.14                      |
| 4.60  | -0.57          | 1.10                    | 1.10                      |
| 4.80  | -0.61          | 1.16                    | 1.16                      |
| 5.00  | -0.59          | 1.08                    | 1.09                      |
| 5.20  | -0.63          | 1.16                    | 1.16                      |
| 5.40  | -0.63          | 1.08                    | 1.10                      |
| 5.60  | -0.65          | 1.12                    | 1.12                      |
| 5.80  | -0.66          | 1.12                    | 1.13                      |
| 6.00  | -0.66          | 1.10                    | 1.10                      |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
086-12MCRNB+  
8/26/2026  
Page 1 of 1