

# Handflex Cable, SMA RA to MCX RA, 12"

086-12SMRMCR+

## Typical Performance Data

| FREQ. | INSERTION LOSS | Right Angle SMA<br>VSWR | Right Angle MCX<br>VSWR |
|-------|----------------|-------------------------|-------------------------|
| (GHz) | (dB)           | (:1)                    | (:1)                    |
| 0.10  | -0.09          | 1.02                    | 1.03                    |
| 0.20  | -0.12          | 1.02                    | 1.02                    |
| 0.40  | -0.18          | 1.01                    | 1.02                    |
| 0.60  | -0.23          | 1.02                    | 1.02                    |
| 0.80  | -0.28          | 1.02                    | 1.04                    |
| 1.00  | -0.31          | 1.01                    | 1.04                    |
| 1.20  | -0.35          | 1.03                    | 1.04                    |
| 1.40  | -0.38          | 1.03                    | 1.06                    |
| 1.60  | -0.40          | 1.03                    | 1.05                    |
| 1.80  | -0.43          | 1.05                    | 1.07                    |
| 2.00  | -0.45          | 1.05                    | 1.08                    |
| 2.20  | -0.48          | 1.04                    | 1.07                    |
| 2.40  | -0.50          | 1.07                    | 1.09                    |
| 2.60  | -0.52          | 1.06                    | 1.08                    |
| 2.80  | -0.54          | 1.08                    | 1.09                    |
| 3.00  | -0.56          | 1.08                    | 1.10                    |
| 3.20  | -0.56          | 1.07                    | 1.10                    |
| 3.40  | -0.59          | 1.10                    | 1.12                    |
| 3.60  | -0.60          | 1.08                    | 1.11                    |
| 3.80  | -0.62          | 1.10                    | 1.12                    |
| 4.00  | -0.64          | 1.11                    | 1.13                    |
| 4.20  | -0.64          | 1.09                    | 1.11                    |
| 4.40  | -0.67          | 1.12                    | 1.15                    |
| 4.60  | -0.67          | 1.09                    | 1.12                    |
| 4.80  | -0.69          | 1.11                    | 1.13                    |
| 5.00  | -0.71          | 1.11                    | 1.13                    |
| 5.20  | -0.72          | 1.10                    | 1.12                    |
| 5.40  | -0.75          | 1.11                    | 1.13                    |
| 5.60  | -0.75          | 1.10                    | 1.12                    |
| 5.80  | -0.76          | 1.10                    | 1.12                    |
| 6.00  | -0.77          | 1.09                    | 1.11                    |



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

IF/RF MICROWAVE COMPONENTS

REV. OR  
086-12SMRMCR+  
8/26/2026  
Page 1 of 1