

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100.0	0.09	42.4	41.5
200.0	0.13	46.1	44.4
300.0	0.16	51.0	46.1
400.0	0.19	43.9	40.4
500.0	0.21	39.9	39.0
600.0	0.23	50.3	44.8
700.0	0.25	39.7	38.9
800.0	0.28	38.5	38.1
1000.0	0.31	36.9	36.6
1100.0	0.33	40.8	40.3
1250.0	0.36	35.7	35.7
1500.0	0.40	34.1	34.6
1750.0	0.43	42.7	40.4
2000.0	0.47	35.8	38.1
2001.0	0.47	35.7	38.0
2250.0	0.50	43.4	48.2
2500.0	0.54	37.6	45.0
2750.0	0.57	37.3	40.3
3000.0	0.59	31.4	30.9
3250.0	0.63	27.6	28.2
3500.0	0.66	27.8	28.0
3750.0	0.70	27.4	27.5
4000.0	0.73	27.6	27.2
4250.0	0.76	26.9	26.8
4500.0	0.77	30.8	30.8
5000.0	0.83	33.9	34.4
5500.0	0.89	49.1	36.6
6000.0	0.93	39.5	45.0
6500.0	0.98	29.3	31.0
7000.0	1.04	28.4	28.8
7500.0	1.07	27.8	29.7
8000.0	1.10	38.9	39.1
8500.0	1.13	43.7	36.3
9000.0	1.17	27.6	26.0
10000.0	1.22	28.0	28.0
10500.0	1.24	35.2	41.4
11000.0	1.26	39.4	30.1
11500.0	1.29	30.5	30.1
12000.0	1.30	34.6	29.8
12500.0	1.33	32.9	28.5
13000.0	1.38	24.4	22.7
13500.0	1.40	25.1	22.4
14000.0	1.40	32.0	27.0
14500.0	1.40	29.4	33.6
15000.0	1.47	26.5	28.9
15500.0	1.52	23.7	26.2
16000.0	1.53	27.6	27.2
16500.0	1.54	36.0	35.9
17000.0	1.63	26.5	21.8
17500.0	1.72	24.8	20.7
18000.0	1.68	25.6	20.3