

Handflex Cable, MCX RA to N Female Bulkhead, 24"

086-24MCRNB+

Typical Performance Data

FREQ.	INSERTION LOSS	Right Angle MCX VSWR	N Female Bulkhead VSWR
(GHz)	(dB)	(:1)	(:1)
0.10	-0.15	1.02	1.03
0.20	-0.23	1.04	1.03
0.40	-0.34	1.07	1.03
0.60	-0.42	1.05	1.03
0.80	-0.49	1.05	1.05
1.00	-0.55	1.05	1.05
1.20	-0.60	1.05	1.07
1.40	-0.65	1.06	1.07
1.60	-0.68	1.04	1.06
1.80	-0.71	1.05	1.06
2.00	-0.78	1.11	1.09
2.20	-0.82	1.07	1.09
2.40	-0.84	1.07	1.09
2.60	-0.89	1.11	1.09
2.80	-0.95	1.10	1.10
3.00	-1.00	1.09	1.11
3.20	-1.04	1.11	1.13
3.40	-1.05	1.12	1.14
3.60	-1.07	1.12	1.15
3.80	-1.13	1.12	1.16
4.00	-1.13	1.13	1.16
4.20	-1.13	1.15	1.16
4.40	-1.12	1.15	1.17
4.60	-1.21	1.14	1.19
4.80	-1.27	1.14	1.20
5.00	-1.25	1.16	1.20
5.20	-1.25	1.19	1.19
5.40	-1.29	1.16	1.20
5.60	-1.30	1.17	1.21
5.80	-1.33	1.18	1.20
6.00	-1.34	1.14	1.18



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 • Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

IF/RF MICROWAVE COMPONENTS

REV. OR
086-24MCRNB+
8/26/2026
Page 1 of 1