

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10.0	0.01	46.3	47.4
50.0	0.02	47.4	51.4
100.0	0.03	46.7	45.9
150.0	0.03	45.8	45.5
200.0	0.04	44.8	44.1
250.0	0.04	43.3	43.0
300.0	0.05	42.4	42.5
350.0	0.05	41.4	41.3
400.0	0.05	40.5	40.5
450.0	0.06	40.0	39.9
500.0	0.06	39.5	39.4
550.0	0.07	39.0	39.2
600.0	0.07	39.0	39.1
650.0	0.07	39.0	38.9
700.0	0.07	39.2	39.2
750.0	0.08	39.4	39.6
800.0	0.08	39.9	39.9
850.0	0.08	40.5	40.5
900.0	0.08	41.4	41.4
950.0	0.09	42.7	42.4
1000.0	0.09	44.3	43.6
1200.0	0.10	50.8	47.8
1400.0	0.10	42.7	42.5
1600.0	0.11	38.8	38.6
1800.0	0.12	37.8	37.5
2000.0	0.13	39.2	39.5
2200.0	0.13	44.2	45.1
2400.0	0.14	47.0	50.1
2600.0	0.14	39.1	38.7
2800.0	0.15	35.2	35.2
3000.0	0.16	34.3	34.1
3600.0	0.17	36.7	36.1
4000.0	0.18	31.0	30.2
4600.0	0.20	32.5	32.8
5000.0	0.21	31.8	30.5
5600.0	0.23	28.8	28.8
6000.0	0.23	29.0	27.4
6600.0	0.26	26.5	26.5
7000.0	0.26	28.4	26.0
7600.0	0.27	25.6	25.8
8000.0	0.28	25.6	23.6
8600.0	0.29	24.2	24.1
9000.0	0.31	24.0	22.8
9600.0	0.32	23.3	23.4
10000.0	0.34	21.4	21.1
10600.0	0.33	23.6	23.5
11000.0	0.37	21.3	21.6
11600.0	0.35	24.2	24.4
12000.0	0.39	20.3	20.7
12600.0	0.37	26.1	25.5
13000.0	0.39	21.7	22.1
13600.0	0.38	28.2	27.6
14000.0	0.41	21.9	22.0
14600.0	0.40	27.8	26.6
15000.0	0.42	24.9	24.6
15600.0	0.43	27.7	27.1
16000.0	0.45	25.2	25.1
16600.0	0.44	26.7	27.0
17000.0	0.48	24.8	25.0
17600.0	0.46	28.1	31.6
18000.0	0.48	24.8	24.5