

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.03	46.5	46.2
200.0	0.05	42.1	44.3
300.0	0.06	40.6	39.7
400.0	0.08	37.6	36.8
500.0	0.09	39.6	41.4
600.0	0.10	43.2	43.3
700.0	0.11	41.5	41.4
800.0	0.12	45.2	43.2
900.0	0.12	46.5	48.0
1000.0	0.13	44.3	45.0
1100.0	0.14	36.9	37.8
1250.0	0.15	35.7	35.0
1500.0	0.17	41.9	35.8
1750.0	0.18	47.9	43.2
2000.0	0.20	38.1	36.5
2001.0	0.20	38.2	36.5
2250.0	0.20	35.7	33.2
2500.0	0.21	45.7	48.2
2750.0	0.22	42.3	31.2
3000.0	0.23	31.6	31.8
3250.0	0.24	33.2	31.0
3500.0	0.25	31.5	29.0
3750.0	0.27	28.7	26.9
4000.0	0.27	32.0	35.8
4250.0	0.28	37.8	32.4
4500.0	0.30	28.0	28.4
5000.0	0.29	34.2	30.7
5500.0	0.30	32.3	31.7
6000.0	0.30	30.1	28.9
6500.0	0.31	40.6	48.3
7000.0	0.33	38.3	32.1
7500.0	0.34	38.5	37.3
8000.0	0.34	31.1	30.4
8500.0	0.36	34.8	31.2
9000.0	0.36	37.3	33.6
9500.0	0.38	29.9	28.4
10000.0	0.39	35.1	32.1
10500.0	0.41	37.5	49.6
11000.0	0.40	35.3	35.5
11500.0	0.43	33.3	29.8
12000.0	0.43	34.2	51.9
12500.0	0.49	30.3	31.2
13000.0	0.42	32.7	32.2
13500.0	0.44	35.4	33.9
14000.0	0.52	29.1	32.2
14500.0	0.48	28.0	27.6
15000.0	0.51	44.6	39.2
15500.0	0.51	31.1	28.3
16000.0	0.53	30.3	30.5
16500.0	0.53	37.1	32.1
17000.0	0.53	34.0	29.4
17500.0	0.62	28.2	28.9
18000.0	0.57	27.6	24.9