

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.04	46.8	46.6
200.0	0.07	43.1	42.3
300.0	0.08	40.3	40.2
400.0	0.10	39.5	39.4
500.0	0.11	42.3	42.6
600.0	0.13	54.0	48.2
700.0	0.14	43.7	40.2
800.0	0.15	36.7	36.4
900.0	0.16	34.6	34.2
1000.0	0.17	35.0	35.6
1100.0	0.18	39.4	39.8
1250.0	0.20	40.9	39.5
1500.0	0.22	32.0	32.5
2000.0	0.27	34.5	35.0
2001.0	0.27	34.5	35.1
2250.0	0.29	52.2	43.6
2500.0	0.31	34.2	33.6
2750.0	0.33	48.4	40.6
3000.0	0.35	34.1	35.2
3250.0	0.37	40.7	33.8
3500.0	0.39	38.1	34.6
3750.0	0.42	40.0	30.3
4000.0	0.44	30.4	28.7
4250.0	0.46	37.0	30.0
4500.0	0.49	26.8	27.1
5000.0	0.52	28.0	29.9
5500.0	0.56	29.1	27.7
6000.0	0.59	25.6	30.0
6500.0	0.62	29.7	34.3
7000.0	0.65	31.5	30.8
7500.0	0.66	28.4	35.8
8000.0	0.68	30.9	34.2
8500.0	0.70	30.2	34.9
9000.0	0.71	27.2	29.1
9500.0	0.74	43.1	26.7
10000.0	0.74	29.5	30.2
10500.0	0.77	35.1	25.3
11000.0	0.76	49.8	31.4
11500.0	0.78	38.6	30.7
12000.0	0.74	34.5	30.8
12500.0	0.81	28.3	26.9
13000.0	0.74	26.3	29.0
13500.0	0.83	24.4	23.5
14000.0	0.77	25.9	24.8
14500.0	0.78	25.8	24.7
15000.0	0.81	26.5	24.4
15500.0	0.81	33.4	28.1
16000.0	0.80	31.3	30.6
16500.0	0.82	33.4	27.6
17000.0	0.83	26.5	28.2
17500.0	0.80	25.7	25.8
18000.0	0.91	20.3	19.6