

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	SMP-FEMALE RETURN LOSS (dB)
10	0.02	49.41	55.15
100	0.05	40.02	41.92
200	0.07	39.86	40.21
300	0.09	45.84	42.42
400	0.11	54.88	48.21
500	0.12	43.37	66.47
600	0.13	39.89	49.93
700	0.14	40.72	48.78
800	0.15	46.11	48.70
900	0.16	54.31	46.54
1000	0.17	41.25	45.37
1100	0.18	38.55	47.21
1200	0.18	40.03	53.40
1300	0.19	46.39	53.93
1400	0.20	45.62	45.05
1500	0.20	39.44	42.05
1600	0.21	37.58	41.27
1800	0.22	43.17	42.94
2000	0.23	36.22	38.39
2500	0.26	35.06	35.75
3000	0.29	34.74	32.68
3500	0.31	36.51	31.68
4000	0.33	35.31	30.84
4500	0.35	36.45	30.49
5000	0.37	31.21	33.25
5500	0.39	30.54	33.41
6000	0.41	30.77	32.20
6500	0.42	28.98	32.90
7000	0.44	29.88	34.60
7500	0.46	28.90	32.57
8000	0.47	29.10	32.63
8500	0.49	27.08	27.72
9000	0.51	28.02	28.36
9500	0.53	25.92	25.75
10000	0.54	26.35	26.77
10500	0.55	25.38	26.78
11000	0.57	24.20	26.98
11500	0.57	24.90	29.03
12000	0.59	23.34	28.37
12500	0.60	23.96	30.29
13000	0.61	23.12	27.62
13500	0.62	25.69	35.77
14000	0.63	25.54	28.17
14500	0.65	25.35	27.37
15000	0.66	28.78	26.03
15500	0.67	33.38	27.55
16000	0.69	33.04	25.96
16500	0.71	26.31	23.55
17000	0.72	24.44	22.81
17500	0.74	22.17	21.60
18000	0.78	20.15	19.47