

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE RETURN LOSS (dB)
10.0	0.02	47.6	45.8
50.0	0.04	44.0	42.9
100.0	0.05	42.0	41.9
140.0	0.06	41.0	41.6
220.0	0.08	40.5	40.7
260.0	0.09	40.5	40.6
300.0	0.09	40.8	40.9
340.0	0.10	41.7	41.3
380.0	0.11	43.5	42.2
460.0	0.11	47.4	45.1
500.0	0.12	47.0	46.1
550.0	0.13	44.1	44.8
600.0	0.13	41.1	42.0
650.0	0.14	39.1	39.5
700.0	0.15	37.8	37.8
750.0	0.15	37.4	37.1
800.0	0.15	37.8	37.2
850.0	0.16	39.0	38.2
900.0	0.16	41.1	40.5
950.0	0.16	43.5	45.4
1000.0	0.17	43.7	55.0
1200.0	0.19	35.8	35.3
1400.0	0.20	41.9	40.9
1500.0	0.21	43.6	48.5
1600.0	0.22	36.3	36.1
1800.0	0.24	36.2	35.1
2000.0	0.25	39.9	39.9
2400.0	0.27	50.0	50.8
2600.0	0.29	30.8	30.3
3000.0	0.31	34.3	33.2
3400.0	0.33	40.8	37.1
3600.0	0.34	28.9	28.5
4000.0	0.36	31.1	30.9
4400.0	0.38	33.4	33.6
4600.0	0.39	28.1	27.8
5000.0	0.41	26.5	26.3
5400.0	0.43	27.8	27.7
5600.0	0.44	26.8	26.0
6000.0	0.45	26.1	25.1
6400.0	0.47	27.7	26.9
6600.0	0.48	30.2	29.5
7000.0	0.50	29.3	28.2
7400.0	0.50	27.3	25.9
7600.0	0.51	33.7	33.2
8000.0	0.53	27.8	27.3
8400.0	0.55	28.2	27.3
8600.0	0.55	29.8	29.0
9000.0	0.56	28.2	28.6
9200.0	0.56	39.3	31.9
9400.0	0.58	26.9	27.3
9600.0	0.59	32.3	29.5
9800.0	0.59	27.3	27.1
10000.0	0.60	26.7	26.1
11600.0	0.65	37.0	33.5
12000.0	0.67	38.2	34.5
12400.0	0.69	27.5	27.1
12800.0	0.73	21.6	21.7
13600.0	0.77	20.5	20.4
14000.0	0.74	24.5	24.5
14400.0	0.73	28.8	28.7
14800.0	0.76	39.5	38.7
15600.0	0.81	22.1	22.7
16000.0	0.84	21.1	21.5
16400.0	0.85	21.9	21.9
17600.0	0.85	27.7	27.3
18000.0	0.84	39.1	38.6