

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.00	48.41	44.21
50.0	0.02	50.63	50.93
100.0	0.03	47.85	47.91
200.0	0.04	44.05	44.80
300.0	0.06	45.89	45.64
400.0	0.07	50.41	52.12
500.0	0.07	56.51	51.75
600.0	0.08	44.15	42.80
700.0	0.09	40.36	40.49
800.0	0.09	42.74	42.62
900.0	0.10	47.76	48.50
1000.0	0.11	45.86	51.04
1100.0	0.11	41.89	44.30
1250.0	0.12	43.33	43.70
1500.0	0.14	42.55	47.19
1750.0	0.15	53.65	54.64
2000.0	0.16	44.01	43.88
2001.0	0.16	44.08	43.72
2250.0	0.17	46.40	51.90
2500.0	0.19	41.31	41.00
2750.0	0.20	51.50	56.03
3000.0	0.21	38.22	38.43
3250.0	0.22	51.15	47.46
3500.0	0.23	37.97	37.41
3750.0	0.24	58.11	63.40
4000.0	0.25	37.92	37.74
4250.0	0.26	46.83	47.67
4500.0	0.27	38.83	39.97
5000.0	0.29	37.19	38.19
5500.0	0.30	38.53	41.69
6000.0	0.32	46.50	47.52
6500.0	0.34	39.40	41.41
7000.0	0.35	37.81	36.80
7500.0	0.35	37.18	39.53
8000.0	0.36	38.14	43.86
8500.0	0.37	41.93	44.85
9000.0	0.34	35.15	32.57
9500.0	0.36	32.42	30.67
10000.0	0.47	35.52	36.51
10500.0	0.52	40.29	42.73
11000.0	0.48	48.05	51.11
11500.0	0.47	32.00	33.50
12000.0	0.44	36.88	31.13
12500.0	0.39	31.04	31.19
13000.0	0.46	31.31	29.76
13500.0	0.52	30.37	42.03
14000.0	0.55	33.76	45.85
14500.0	0.55	42.28	30.04
15000.0	0.51	31.73	33.00
15500.0	0.54	25.98	24.82
16000.0	0.60	22.48	25.00
16500.0	0.62	25.81	30.05
17000.0	0.65	35.29	29.63
17500.0	0.71	25.81	24.63
18000.0	0.71	25.16	25.51