

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.10	42.8	43.3
200	0.14	43.8	42.8
300	0.17	44.2	43.1
400	0.20	41.4	43.2
500	0.22	41.4	42.3
600	0.25	40.6	42.3
700	0.26	40.3	41.7
800	0.29	39.8	40.1
900	0.32	38.8	38.7
1000	0.32	39.9	38.4
1100	0.34	39.0	38.6
1250	0.36	36.0	36.2
1500	0.40	35.7	35.7
1750	0.43	35.1	34.7
2000	0.47	32.6	33.8
2250	0.49	33.6	35.0
2500	0.52	34.7	35.3
2750	0.55	35.6	37.7
3000	0.58	35.2	37.0
3250	0.61	37.5	37.5
3500	0.63	37.4	35.7
3750	0.67	34.5	34.7
4000	0.69	33.7	33.9
4250	0.72	34.6	32.1
4500	0.73	35.1	34.2
5000	0.78	35.7	37.1
5500	0.81	35.6	36.1
6000	0.87	32.8	33.4
6500	0.94	30.7	31.4
7000	1.01	32.8	32.4
7500	1.06	32.4	36.9
8000	1.08	29.3	25.6
8500	1.10	25.5	25.6
9000	1.15	23.1	22.5
9500	1.16	23.4	23.8
10000	1.12	26.1	28.7
11000	1.25	26.1	24.6
12000	1.30	23.8	23.9
13000	1.38	26.7	27.6
13500	1.46	22.2	22.9
14000	1.50	23.4	23.4
14500	1.49	22.4	21.9
15000	1.61	23.5	23.1
15500	1.57	26.6	26.3
16000	1.66	21.1	22.8
16500	1.69	22.1	22.7
17000	1.70	20.3	20.5
17500	1.81	20.6	23.0
18000	1.79	22.9	21.7