

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.01	37.15	37.46
50.0	0.01	60.78	58.42
100.0	0.01	59.21	63.21
200.0	0.02	48.54	48.65
300.0	0.02	44.90	44.69
400.0	0.02	42.40	41.51
500.0	0.03	40.27	39.49
600.0	0.03	38.36	37.73
700.0	0.03	37.53	36.68
800.0	0.03	37.07	36.60
900.0	0.03	37.22	36.69
1000.0	0.04	37.90	37.64
1100.0	0.04	38.75	38.91
1500.0	0.04	50.88	58.20
2250.0	0.06	38.75	37.93
2500.0	0.06	38.92	35.40
2750.0	0.06	40.24	36.33
3000.0	0.06	41.20	40.33
3250.0	0.07	43.03	40.28
3500.0	0.07	47.00	41.60
3750.0	0.07	47.96	44.76
4000.0	0.08	42.57	39.47
4250.0	0.07	41.30	37.51
4500.0	0.07	42.65	37.49
4750.0	0.09	44.32	37.52
5000.0	0.09	41.49	34.74
5250.0	0.10	38.01	33.35
5500.0	0.10	33.98	35.51
5750.0	0.11	32.78	34.87
6000.0	0.11	34.87	34.47
6500.0	0.11	38.25	40.98
7000.0	0.14	29.94	29.54
7500.0	0.13	32.15	34.16
8000.0	0.14	45.93	39.02
8500.0	0.17	29.17	33.46
9000.0	0.16	29.67	30.02
9500.0	0.15	48.53	48.47
10000.0	0.13	31.51	35.95
10500.0	0.18	33.12	35.11
11000.0	0.18	50.13	44.51
11250.0	0.17	43.94	38.42
11500.0	0.16	38.24	33.76
12000.0	0.21	38.17	31.63
12500.0	0.20	38.02	37.70
13000.0	0.18	51.16	34.14
13500.0	0.18	42.05	31.07
14000.0	0.16	34.62	38.54
14500.0	0.19	39.80	27.98
15000.0	0.21	35.87	29.08
15500.0	0.16	40.69	38.18
16000.0	0.23	34.58	27.47
16500.0	0.28	45.76	35.49
17000.0	0.24	30.49	27.47
17500.0	0.31	34.00	27.06
18000.0	0.30	36.19	34.32