

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1	80.65	0.00	430	5.50
10	61.00	0.00	434	5.27
100	43.83	0.09	438	5.07
150	43.20	0.23	442	4.89
200	43.58	0.45	446	4.73
260	44.06	0.86	450	4.58
300	49.67	1.30	454	4.47
320	36.15	1.60	458	4.33
330	30.56	1.79	462	4.26
340	25.67	2.03	466	4.13
350	21.20	2.34	470	4.06
360	17.05	2.76	474	3.96
370	13.26	3.42	478	3.91
380	9.93	4.47	482	3.85
390	7.25	6.11	486	3.76
400	5.34	8.45	490	3.72
420	3.42	14.56	494	3.64
430	2.99	17.75	498	3.60
450	2.55	23.72	502	3.56
460	2.42	26.75	506	3.54
530	2.23	20.66	510	3.51
630	3.23	15.19	514	3.46
650	4.03	11.59	518	3.41
660	4.66	9.61	522	3.41
700	9.11	4.49	526	3.38
710	10.62	3.88	530	3.38
760	18.98	2.53	534	3.35
770	20.70	2.42	538	3.33
800	25.86	2.19	542	3.31
830	30.97	2.02	546	3.31
850	34.37	1.92	550	3.29
900	43.48	1.66	554	3.29
950	57.15	1.41	558	3.27
1000	46.63	1.20	562	3.27
1200	36.85	0.78	566	3.28
1300	36.81	0.72	570	3.30
1400	38.07	0.71	574	3.31
1500	40.71	0.72	578	3.34
1800	45.76	0.79	600	3.45
2000	35.28	0.88	630	3.89