

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.00	41.9	44.1
200.0	0.01	37.2	38.2
300.0	0.01	34.0	34.5
400.0	0.02	32.0	33.1
500.0	0.02	31.5	32.8
600.0	0.02	32.3	32.5
700.0	0.03	33.2	33.9
800.0	0.03	38.8	39.3
900.0	0.03	43.7	46.4
1000.0	0.03	42.4	46.8
1100.0	0.03	34.2	35.5
1250.0	0.03	31.1	31.9
1500.0	0.04	35.2	35.3
1750.0	0.03	42.6	51.4
2000.0	0.05	29.6	29.7
2250.0	0.05	26.7	26.4
2500.0	0.05	31.7	31.0
2750.0	0.05	40.7	39.4
3000.0	0.05	35.8	34.1
3250.0	0.05	38.4	34.7
3500.0	0.06	40.5	43.8
3750.0	0.06	31.9	31.3
4000.0	0.07	31.5	31.2
4250.0	0.06	42.7	42.9
4500.0	0.06	51.8	43.6
5000.0	0.07	44.4	52.4
5500.0	0.08	32.7	31.6
6000.0	0.08	43.8	41.0
6500.0	0.10	29.3	29.2
7000.0	0.10	42.3	36.6
7500.0	0.11	26.7	26.1
8000.0	0.10	49.3	40.8
8500.0	0.12	25.2	24.8
9000.0	0.13	31.2	34.5
9500.0	0.15	25.1	25.5
10000.0	0.12	28.7	27.2
10500.0	0.14	26.3	26.6
11000.0	0.13	27.5	26.3
11500.0	0.13	28.7	31.6
12000.0	0.17	24.8	25.0
12500.0	0.16	28.7	33.1
13000.0	0.17	25.4	28.9
13500.0	0.18	30.0	35.0
14000.0	0.18	30.9	34.2
14500.0	0.20	33.5	43.1
15000.0	0.21	39.4	32.8
15500.0	0.22	30.1	32.5
16000.0	0.24	34.8	37.0
16500.0	0.24	28.0	35.8
17000.0	0.24	29.1	26.1
17500.0	0.30	22.9	24.3
18000.0	0.28	28.2	31.6