

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-FEMALE BULKHEAD RETURN LOSS (dB)
100.0	0.02	45.7	46.4
200.0	0.03	43.8	42.4
400.0	0.04	37.6	37.0
500.0	0.04	36.0	36.2
600.0	0.04	35.5	36.4
800.0	0.05	39.5	41.5
900.0	0.06	46.0	48.0
1000.0	0.06	48.8	48.8
1200.0	0.07	37.6	37.4
1400.0	0.08	34.0	34.3
1600.0	0.08	35.4	36.7
2000.0	0.10	39.6	39.3
2200.0	0.08	32.5	34.4
2400.0	0.07	33.9	35.4
2600.0	0.08	38.6	38.8
2800.0	0.07	38.2	37.8
3000.0	0.09	34.2	36.3
3200.0	0.09	33.1	35.3
3400.0	0.10	34.3	34.2
3600.0	0.11	37.3	36.3
3800.0	0.09	38.1	38.9
4000.0	0.11	32.9	34.2
4200.0	0.11	30.0	30.6
4400.0	0.11	31.5	32.8
4600.0	0.12	32.4	36.0
4800.0	0.11	29.6	32.8
5000.0	0.13	27.0	29.7
5200.0	0.13	27.9	30.7
5400.0	0.13	27.7	32.6
5600.0	0.14	25.9	31.1
5800.0	0.12	24.9	29.0
6000.0	0.18	25.6	28.9
6200.0	0.14	25.6	30.8
6400.0	0.15	24.0	29.4
6600.0	0.16	23.4	27.1
6800.0	0.14	24.2	27.0
7000.0	0.16	24.3	28.3
7400.0	0.16	23.9	27.5
7600.0	0.21	25.5	27.3
7800.0	0.17	24.7	27.9
8000.0	0.19	23.5	27.8
8200.0	0.18	24.3	26.7
8400.0	0.19	25.3	25.8
8600.0	0.19	24.0	26.0
8800.0	0.19	24.2	27.7
9000.0	0.19	27.5	30.2
9200.0	0.19	29.7	29.8
9400.0	0.19	26.3	28.0
9600.0	0.20	26.3	29.0
9800.0	0.20	30.3	32.4
10000.0	0.25	32.4	32.7
10200.0	0.23	29.7	29.8
10400.0	0.23	33.2	32.2
10600.0	0.24	34.4	30.6
11000.0	0.25	34.5	26.6
11200.0	0.25	34.9	26.9
12400.0	0.29	26.9	20.3
12500.0	0.29	27.5	20.2