

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.01	47.4	48.2
200.0	0.02	42.7	43.8
300.0	0.03	40.5	40.9
500.0	0.03	42.4	43.1
600.0	0.04	48.6	49.3
800.0	0.04	46.6	46.8
900.0	0.05	41.6	40.7
1000.0	0.05	39.9	37.8
1200.0	0.07	43.8	37.3
1400.0	0.06	52.0	48.0
1600.0	0.07	39.4	40.9
1800.0	0.08	36.5	35.6
2000.0	0.08	38.8	39.6
2200.0	0.07	43.4	41.5
2400.0	0.05	34.0	34.2
2600.0	0.06	33.1	32.4
2800.0	0.09	38.0	33.6
3000.0	0.08	35.2	35.1
3500.0	0.11	32.4	32.4
4000.0	0.13	28.7	30.1
4500.0	0.11	32.5	32.2
5000.0	0.13	27.6	29.9
5500.0	0.07	30.1	40.2
6000.0	0.13	32.6	35.0
6500.0	0.13	28.1	30.7
7000.0	0.11	35.3	35.0
7500.0	0.13	31.2	32.9
8000.0	0.14	34.6	32.5
8500.0	0.13	28.6	29.9
9000.0	0.15	30.2	27.4
9500.0	0.18	30.2	26.3
10000.0	0.17	25.0	24.3
10500.0	0.19	25.7	23.9
11000.0	0.18	25.8	25.4
11500.0	0.20	27.7	25.8
12000.0	0.18	24.9	24.8
12500.0	0.24	30.3	28.8
13000.0	0.14	29.1	27.5
13500.0	0.16	26.1	24.3
14500.0	0.20	29.2	28.0
15000.0	0.16	34.9	27.2
15500.0	0.23	29.3	27.3
17000.0	0.46	23.9	26.3
18000.0	0.45	24.9	23.6