

Coaxial Low Pass Filter

BLP-10.7-75+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)	FREQUENCY (MHz)	GROUP DELAY (nsec)
1.0	0.11	21.77	1.0	68.810
2.6	0.23	16.16	1.1	67.570
4.3	0.24	17.81	1.2	68.380
5.9	0.22	31.76	1.4	67.690
7.5	0.30	23.25	1.5	67.330
9.1	0.37	23.48	1.7	68.360
11.0	0.52	31.19	1.9	68.280
12.4	1.45	10.50	2.1	66.850
14.0	8.90	1.41	2.4	66.160
15.6	19.20	0.40	2.6	67.720
16.3	23.22	0.31	2.9	68.040
17.0	26.93	0.26	3.2	68.320
17.6	29.90	0.23	3.6	69.110
18.3	33.15	0.20	4.0	68.900
19.0	36.20	0.18	4.4	70.180
19.7	39.07	0.17	4.9	71.730
20.6	42.53	0.15	5.5	73.450
21.4	45.54	0.14	6.1	74.720
22.3	48.58	0.13	6.8	76.690
23.1	51.17	0.12	7.5	78.910
24.0	53.98	0.12	8.3	82.640
24.9	56.67	0.11	9.3	88.480
46.8	76.14	0.05	10.3	99.260
68.7	74.18	0.04	11.0	111.040
90.6	73.55	0.04	12.8	151.870
112.5	73.13	0.04	14.0	113.880
134.3	74.86	0.04	16.0	48.350
156.2	73.72	0.05	17.8	28.430
178.1	75.53	0.05	19.0	21.510
200.0	75.97	0.05	22.0	11.340

REV. X1
BLP-10.7-75+
060724
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED • RoHS compliant
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

